

FEATURES

- Surface-mounted door and window switches
- Proximity switch activation
- Normally open configuration
- Switching current of 500 (dc) mA
- Switching voltage of 50 V mA
- Operating gap of 5mm
- White-coloured
- Depth of 8.7 mm
- Height of 14 mm
- Width of 38 mm
- Supplied with fixing screws

RS PRO Door and Window Switch Surface Mount 500 (dc)mA, 50V dc

RS Stock No.: 122-0719



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Looking to safeguard your property? These door and window switches will alert you to intruders. They create a signal that's broken when a door or window is opened, triggering an alarm system.

With a switching current of 500 (dc) mA, they're reliable and unlikely to burn out. A 500 mm cable allows them to be fitted on doors and windows without being restricted to the vicinity of the alarm itself. The cables are PVC-insulated (polyvinyl chloride), so they're durable with low electrical resistance. All of this is housed in a compact design for discreet installation. This product is surface-mounted and supplied with fixing screws.

General Specifications

Activation Type	Proximity Switch
Colour	White
Switch Configuration	Normally Open
Operating Gap	5mm
Applications	Commercial and Residential, Home or Offices

Electrical Specifications

Switching Current	500mA (DC)
Switching Voltage	50VDC
Maximum Power	10 W/VA
Contact Resistance	1Ω Typical

Mechanical Specifications

Mounting Type	Surface Mount
Dimensions	8.7mm x 14mm x 38mm
Depth	8.7mm
Height	14 mm
Width	38mm
Cable length	500mm (24 AWG 4 core PVC insulated cable)

Operation Environment Specifications

Operating Temperature	-10°C to +85°C
------------------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, BS 4737
----------------------------------	-------------------------



