





**DESCRIPTION:**

TVS diodes can be used in a wide range of applications which like consumer electronic products, automotive industries, munitions, telecommunications, aerospace industries, and intelligent control systems.

**Package and Pin Configuration**



SOD123FL



**Maximum Ratings**  $T_A = 25^\circ\text{C}$  unless otherwise specified

PARAMETER	SYMBOL	LIMIT	UNITS
Peak Pulse Power Dissipation( $t_p = 10/1000 \text{ us}$ )	$P_{PP}^{(1,2)}$	400	W
Peak Pulse Current on $t_p = 10/1000 \text{ us}$ waveform <sup>(Fig.2)</sup>	$I_{PPM}^{(1)}$	See table 1	A
ESD IEC61000-4-2(Air)	$V_{ESD}$	$\pm 30$	kV
ESD IEC61000-4-2(Contact)		$\pm 30$	
Typical Thermal Resistance Junction to Ambient	$R_{\theta JA}^{(3)}$	200	$^\circ\text{C/W}$
Operating Junction Temperature Range	$T_J$	-55~150	$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-65~150	$^\circ\text{C}$



TECH PUBLIC

—台舟电子—

TPTVSxS1UR series

SURFACE MOUNT TRANSIENT VOLTAGE SUPPRESSOR

ELECTRICAL CHARACTERISTICS(T<sub>A</sub>=25°C)

WWW.TECHPUBLIC.COM

Part Number	V <sub>RWM</sub>	V <sub>BR</sub>			I <sub>R</sub> @V <sub>RWM</sub>	V <sub>C</sub> @I <sub>PP</sub>	
		Min.	Max.	I <sub>T</sub>		V	A
UNI	V	V	V	mA	uA	V	A
TPTVS6V0S1UR	6	6.67	7.37	10	50	10.3	38.8
TPTVS6V5S1UR	6.5	7.22	7.98	10	40	11.2	35.7
TPTVS7V0S1UR	7	7.78	8.6	10	40	12	33.3
TPTVS7V5S1UR	7.5	8.33	9.21	1	30	12.9	31
TPTVS8V0S1UR	8	8.89	9.83	1	5	13.6	29.4
TPTVS8V5S1UR	8.5	9.44	10.4	1	5	14.4	27.8
TPTVS9V0S1UR	9	10	11.1	1	0.5	15.4	26
TPTVS10VS1UR	10	11.1	12.3	1	0.5	17	23.5
TPTVS11VS1UR	11	12.2	13.5	1	0.5	18.2	22
TPTVS12VS1UR	12	13.3	14.7	1	0.5	19.9	20.1
TPTVS13VS1UR	13	14.4	15.9	1	0.1	21.5	18.6
TPTVS14VS1UR	14	15.6	17.2	1	0.1	23.2	17.2
TPTVS15VS1UR	15	16.7	18.5	1	0.1	24.4	16.4
TPTVS16VS1UR	16	17.8	19.7	1	0.1	26	15.4
TPTVS17VS1UR	17	18.9	20.9	1	0.1	27.6	14.5
TPTVS18VS1UR	18	20	22.1	1	0.1	29.2	13.7
TPTVS20VS1UR	20	22.2	24.5	1	0.1	32.4	12.3
TPTVS22VS1UR	22	24.4	26.9	1	0.1	35.5	11.3
TPTVS24VS1UR	24	26.7	29.5	1	0.1	38.9	10.3
TPTVS26VS1UR	26	28.9	31.9	1	0.1	42.1	9.5
TPTVS28VS1UR	28	31.1	34.4	1	0.1	45.4	8.8
TPTVS30VS1UR	30	33.3	36.8	1	0.1	48.4	8.3
TPTVS33VS1UR	33	36.7	40.6	1	0.1	53.3	7.5
TPTVS36VS1UR	36	40	44.2	1	0.1	58.1	6.9
TPTVS40VS1UR	40	44.4	49.1	1	0.1	64.5	6.2
TPTVS43VS1UR	43	47.8	52.8	1	0.1	69.4	5.8
TPTVS45VS1UR	45	50	55.3	1	0.1	72.2	5.5
TPTVS48VS1UR	48	53.3	58.9	1	0.1	77.4	5.2
TPTVS51VS1UR	51	56.7	62.7	1	0.1	82.4	4.9
TPTVS54VS1UR	54	60	66.3	1	0.1	87.1	4.6
TPTVS58VS1UR	58	64.4	71.2	1	0.1	93.6	4.3
TPTVS60VS1UR	60	66.7	73.7	1	0.1	96.8	4.1
TPTVS64VS1UR	64	71.1	78.6	1	0.1	103	3.9

**RATINGS AND V-I CHARACTERISTICS CURVES** ( $T_A=25^\circ\text{C}$ , unless otherwise noted)

Fig. 1 - Peak Pulse Power Rating Curve




Fig. 2 - Typical Junction Capacitance




Fig. 3 - Pulse Waveform





Fig. 4 - Pulse Derating Curve





**TECH PUBLIC**


—台舟电子—

**TPTVSxS1UR series**

**SURFACE MOUNT TRANSIENT VOLTAGE SUPPRESSOR**

[WWW.TECHPUBLIC.COM](http://WWW.TECHPUBLIC.COM)

**Package Outline Dimensions: SOD-123FL**



SOD-123FL						
Dimension	Inches			Millimeters		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.059		0.079	1.5		2
B	0.134		0.154	3.4		3.9
C	0.028		0.047	0.7		1.2
D	0.098		0.114	2.5		2.9
F	0.002		0.01	0.05		0.26
G	-		0.004	-		0.1
H	0.037		0.053	0.95		1.35
L	0.014		0.035	0.35		0.9

[WWW.SOT23.COM.TW](http://WWW.SOT23.COM.TW)