








A	B	C	D	E																														
			REV.	DESCRIPTION	ECN NO.	NAME	DATE																											
<p>1. Material:</p> <p>1.1 Housing: <b>PBT</b> UL94V-0 Black.</p> <p>1.2 Contact :Phosphor Bronze( C5210),Gold plated on contact area <b>6u"</b>.</p> <p>1.3 Input Terminal : Brass(C2680).</p> <p>1.4 Metal shielding:Copper alloy with Nickel plated(C2680).</p> <p>2.Environmental requirements:</p> <p>2.1 Lead-free process,compliant RoHS.</p>																																		
																																		
																																		
<p>Recommended PCB Layout (Tolerance:±0.05)</p>		<table border="1"> <tr> <td>GENERAL TOLERANCE</td> <td>DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD</td> </tr> <tr> <td>DIM.</td> <td>TOL.</td> </tr> <tr> <td>.x</td> <td>±0.35</td> </tr> <tr> <td>.xx</td> <td>±0.25</td> </tr> <tr> <td>.xxx</td> <td>±0.15</td> </tr> <tr> <td>GENERAL ANGLE:</td> <td></td> </tr> <tr> <td>x.°</td> <td>±3.0°</td> </tr> <tr> <td>x.x°</td> <td>±2.0°</td> </tr> <tr> <td>x.xx°</td> <td>±1.0°</td> </tr> </table> 	GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD	DIM.	TOL.	.x	±0.35	.xx	±0.25	.xxx	±0.15	GENERAL ANGLE:		x.°	±3.0°	x.x°	±2.0°	x.xx°	±1.0°	<table border="1"> <tr> <td colspan="2">TITLE: RJ45 无弹 左绿右黄 B3.05 DIP 100兆</td> </tr> <tr> <td>DWG. NO.: RJ45-911-E55</td> <td>CHECKED: MAX</td> </tr> <tr> <td>PART NO.: RJ45-911-E55</td> <td>DRAWN: ELLA</td> </tr> <tr> <td>UNIT: mm</td> <td>SCALE: none</td> </tr> <tr> <td>SHEET: 1 of 1</td> <td>DWG. SIZE: A4</td> </tr> <tr> <td>LAYER: bxcn</td> <td>APPROVED: WILL</td> </tr> </table>	TITLE: RJ45 无弹 左绿右黄 B3.05 DIP 100兆		DWG. NO.: RJ45-911-E55	CHECKED: MAX	PART NO.: RJ45-911-E55	DRAWN: ELLA	UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxcn	APPROVED: WILL	
GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD																																	
DIM.	TOL.																																	
.x	±0.35																																	
.xx	±0.25																																	
.xxx	±0.15																																	
GENERAL ANGLE:																																		
x.°	±3.0°																																	
x.x°	±2.0°																																	
x.xx°	±1.0°																																	
TITLE: RJ45 无弹 左绿右黄 B3.05 DIP 100兆																																		
DWG. NO.: RJ45-911-E55	CHECKED: MAX																																	
PART NO.: RJ45-911-E55	DRAWN: ELLA																																	
UNIT: mm	SCALE: none																																	
SHEET: 1 of 1	DWG. SIZE: A4																																	
LAYER: bxcn	APPROVED: WILL																																	
		<p>WWW.BXCONN.COM 东莞市宝讯精密技术有限公司</p>	<p>ARTICLE: BX-CN-001-A</p>																															



REV.	DESCRIPTION	ECN NO.	NAME	DATE

3. Electrical Specification @25°C:
- 3.1 Inductance: 350uH Min With 8mA DC bias.
  - 3.2 Insertion loss :
    - 1-100MHZ -1dB max.
  - 3.3 Return loss :
    - 1-30MHZ -18dB min.
    - 30-60MHZ -16dB min.
    - 60-80MHZ -12dB min.
    - 80-100MHZ -10dB min.
  - 3.4 Common Mode Rejection: 1-100MHZ -30dB min.
  - 3.5 Cross Talk: 1-100MHZ -30dB min.
4. Operating and Storage Temperature:
- 4.1 Operating Temperature : -40°C to +85°C.
  - 4.2 Storage Temperature : -40°C to +85°C.
5. Wave soldering peak temperature: 260°C.

Emitting Color	$\lambda_p$ (nm)	$V_f@I_f=20mA$
Green	565	1.8-2.5V
YELLOW	585	1.8-2.5V

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM. TOL. .x ±0.35 .xx ±0.25 .xxx ±0.15 GENERAL ANGLE: x.° ±3.0° x.x° ±2.0° x.xx° ±1.0°		TITLE: RJ45 无弹 左绿右黄 B3.05 DIP 100兆		
UNIT: mm		DWG. NO.: RJ45-911-E55	CHECKED: MAX	
SCALE: none		PART NO.: RJ45-911-E55	DRAWN: ELLA	
SHEET: 1 of 1		DWG. SIZE: A4	APPROVED: WILL	
LAYER: bxconn				

