






REV.	Q'TY	ECN. NO.	APR.	DATE



Part No	Pin	A	B	C
XY-SM02B-SRSS-WB	2	1.00	4.35	2.60
XY-SM03B-SRSS-WB	3	2.00	5.35	3.60
XY-SM04B-SRSS-WB	4	3.00	6.35	4.60
XY-SM05B-SRSS-WB	5	4.00	7.35	5.60
XY-SM06B-SRSS-WB	6	5.00	8.35	6.60
XY-SM07B-SRSS-WB	7	6.00	9.35	7.60
XY-SM08B-SRSS-WB	8	7.00	10.35	8.60
XY-SM09B-SRSS-WB	9	8.00	11.35	9.60
XY-SM10B-SRSS-WB	10	9.00	12.35	10.60
XY-SM11B-SRSS-WB	11	10.00	13.35	11.60
XY-SM12B-SRSS-WB	12	11.00	14.35	12.60
XY-SM13B-SRSS-WB	13	12.00	15.35	13.60
XY-SM14B-SRSS-WB	14	13.00	16.35	14.60
XY-SM15B-SRSS-WB	15	14.00	17.35	15.60
XY-SM16B-SRSS-WB	16	15.00	18.35	16.60
XY-SM20B-SRSS-WB	20	19.00	22.35	20.60

- NOTES:
- 1.BASE: LCP
 - 2.PIN: Brass
 - 3.Solder Tab: Brass
- SPECIFICATIONS:
- 1.Spacing: 1.0
 - 2.Voltage Rating: 50V AC DC
 - 3.Current Rating: 1A AC DC
 - 4.Insulation Resistance: 100MΩ Min
 - 5.Contact Resistance: 30mΩ Max
 - 6.Withstanding voltage: 250V AC 1/Minute
 - 7.Temperatuer Range: -40℃ ~+ 85℃



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: WAFER 1.00 肆肆			
.X±0.2	X.*± 5°	APR.	Alex	DWG NO. XY-SMNB-SRSS-WB	
.XX±0.1	.X.*± 3°	CHK.	Jack	PROJ. CUSTOMER DRAWING	
.XXX±0.05	.XX.*± 1°	DRA.	Can	SIZE A4	SCALE 1:1 SHEET 1/1 REV. A