



0010682


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com




Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010682	N/A	Green

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=430 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	15.89	0.626	16.37	0.645	MAX	
ID (C)	12.05	0.475	11.45	0.451	MIN	
HT (B)	7.85	0.309	8.32	0.328	MAX	

Electrical Characeristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x0.5TSx120mm)			Initial Permeabili-ty	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
@25Mhz	25Ω	26°C	1500	320 (1.6kA/m)	140	7.0	5.1	NZO	3.5
@100Mhz	65Ω	50%							

The Limit of Breakage						Temperature Rating	
Winding Length Per Turn				Wound Coil Dimensions (mm)			Curie Temp: >160°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-	Coating Temp (Continuous up to): 180°C
					HT	-	
				Completely Full Window	Max OD	-	Notes:
					Max HT	-	
-	-	-	-				
-	-	-	-				
-	-	-	-	Surface Area (mm ₂)			
-	-	-	-	Unwound Core	-		
-	-	-	-	40% Winding Factor	-		

IMPEDANCE V.S FREQUENCY



Revision 10/8/2025

