



0010789


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com




Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010789	N/A	No

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=120 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	17.45	0.688	19.20	0.756	MAX	
ID (C)	9.56	0.377	8.80	0.347	MIN	
HT (B)	28.54	1.124	29.68	1.169	MAX	

Electrical Characeristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x0.5TSx120mm)			Initial Permeabili-ty	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
			1200	360 (1.6kA/m)	140	20.0	5.1	NZO	22.0
@25Mhz	100Ω	26°C							
@100Mhz	180Ω	50%							

The Limit of Breakage						Temperature Rating		
Winding Length Per Turn				Wound Coil Dimensions (mm)			Curie Temp: >160°C	
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-	Coating Temp (Continuous up to): 180°C	
					HT	-		
				Completely Full Window	Max OD	-		Notes:
					Max HT	-		
-	-	-	-	Surface Area (mm ₂)				
-	-	-	-					
-	-	-	-					
-	-	-	-					
-	-	-	-	Unwound Core	-			
-	-	-	-	40% Winding Factor	-			

IMPEDANCE V.S FREQUENCY



Revision 10/8/2025

