



0010862


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com



Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010862	N/A	No

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=560 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	18.40	0.725	19.32	0.761	MAX	
ID (C)	11.80	0.465	10.86	0.428	MIN	
HT (B)	6.50	0.256	6.76	0.266	MAX	

Electrical Characteristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x1TSx120mm)			Initial Permeability	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
@25Mhz	40Ω	26°C	1200	360 (<1.6kA/m)	140	20.0	5.1	NZO	3.8
@100Mhz	65Ω	50%							

The Limit of Breakage					Temperature Rating	
Winding Length Per Turn			Wound Coil Dimensions (mm)			Curie Temp: >160°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	Coating Temp (Continuous up to): 180°C
					HT	
-	-	-	-	Completely Full Window	Max OD	Notes:
-	-	-	-		Max HT	
-	-	-	-	Surface Area (mm ²)		
-	-	-	-	Unwound Core	-	
-	-	-	-	40% Winding Factor	-	

IMPEDANCE V.S FREQUENCY

