

## Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	$I_D$
60V	1.05mΩ@10V	325A



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


## Feature

- Fast Switching
- Low Gate Charge and R<sub>ds(on)</sub>
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test


## Applications

- Power switching application
- DC-DC Converter
- Power Management


## Package



## Circuit diagram



## Marking



SP60N01GHTO : Product code  
 \*\* : Week code

## Order Information

Device	Package	Unit/Tape
SP60N01GHTO	TOLL	2000

**Absolute maximum ratings (Ta=25°C unless otherwise noted)**

Parameter	Symbol	Rating	Units
Drain-Source Voltage	$V_{DS}$	60	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current (Tc=25°C)	$I_D$	325	A
Continuous Drain Current (Tc=100°C)	$I_D$	217	A
Pulsed Drain Current	$I_{DM}$	1300	A
Single Pulse Avalanche Energy <sup>1</sup>	$E_{AS}$	1600	mJ
Power Dissipation (Tc=25°C)	$P_D$	475	W
Power Dissipation (Tc=100°C)	$P_D$	190	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.26	°C/W
Storage Temperature Range	$T_{STG}$	-55 to 150	°C
Operating Junction Temperature Range	$T_J$	-55 to 150	°C


**Electrical characteristics (Ta=25°C, unless otherwise noted)**

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
<b>Static Characteristics</b>						
Drain-Source Breakdown Voltage	$BV_{DSS}$	$V_{GS}=0V, I_D=250\mu A$	60	-	-	V
Drain-Source Leakage Current	$I_{DSS}$	$V_{DS}=48V, V_{GS}=0V$	-	-	1	$\mu A$
Gate-Source Leakage Current	$I_{GSS}$	$V_{GS}=\pm 20V, V_{DS}=0V$	-	-	$\pm 100$	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{GS}=V_{DS}, I_D=250\mu A$	2.4	2.8	3.4	V
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS}=10V, I_D=30A$	-	1.05	1.3	m $\Omega$
Gate Resistance	$R_G$	$V_{DS}=30V, V_{GS}=0V, f=1MHz$	-	1.03	-	$\Omega$
<b>Dynamic characteristics</b>						
Input Capacitance	$C_{iss}$	$V_{DS}=30V, V_{GS}=0V, f=1MHz$	-	6430	-	pF
Output Capacitance	$C_{oss}$		-	2714	-	
Reverse Transfer Capacitance	$C_{rss}$		-	151	-	
Total Gate Charge	$Q_g$	$V_{DS}=30V, V_{GS}=10V, I_D=50A$	-	91	-	nC
Gate-Source Charge	$Q_{gs}$		-	18	-	
Gate-Drain Charge	$Q_{gd}$		-	22	-	
Gate Plateau Voltage	$V_{plateau}$		-	4.9	-	
<b>Switching Characteristics</b>						
Turn-On Delay Time	$T_{d(on)}$	$V_{DD}=30V, V_{GS}=10V, R_G=3\Omega, I_D=50A$	-	36	-	nS
Rise Time	$T_r$		-	72	-	
Turn-Off Delay Time	$T_{d(off)}$		-	76	-	
Fall Time	$T_f$		-	54	-	
<b>Diode Characteristics</b>						
Diode Forward Voltage	$V_{SD}$	$V_{GS}=0V, I_S=1A, T_J=25^\circ C$	-	-	1.2	V
Maximum Body-Diode Continuous Current	$I_S$		-	-	325	A
Reverse Recovery Time	$T_{rr}$	$I_S=50A, di/dt=100A/\mu s, T_J=25^\circ C$	-	88	-	nS
Reverse Recovery Charge	$Q_{rr}$		-	126	-	nC


**Note :**

1. The test condition is  $V_{DD}=30V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$


**Typical Characteristics**




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




RDS(on) VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage







Normalized Threshold voltage




Safe Operation Area



**Test Circuit**



**Temperature Profile for IR Reflow Soldering**



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
<b>Preheat &amp; Soak</b>		
Temperature min (T <sub>Smin</sub> )	100°C	150°C
Temperature max (T <sub>Smax</sub> )	150°C	200°C
Time (T <sub>Smin</sub> to T <sub>Smax</sub> ) (t <sub>s</sub> )	60-120 seconds	60-120 seconds
Average ramp-up rate (T <sub>Smax</sub> to T <sub>p</sub> )	3 °C/second max.	3°C/second max.
Liquidous temperature (T <sub>L</sub> )	183 °C	217°C
Time at liquidous (t <sub>L</sub> )	60-150 seconds	60-150 seconds
Peak package body Temperature e (T <sub>p</sub> )*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t <sub>p</sub> )** within 5°C of the specified classification temperature (T <sub>c</sub> )	20** seconds	30** seconds
Average ramp-down rate (T <sub>p</sub> to T <sub>Smax</sub> )	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T <sub>p</sub> ) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t <sub>p</sub> ) is defined as a supplier minimum and a user maximum		

Table 1. SnPb Eutectic Process – Classification Temperatures (T<sub>c</sub>)



Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T<sub>c</sub>)


Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350-2000	Volume mm <sup>3</sup> >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

## TOLL Reel Information

REEL DIMENSIONS



TAPE DIMENSIONS




- A0: Dimension designed to accommodate the component width
- B0: Dimension designed to accommodate the component length
- K0: Dimension designed to accommodate the component thickness
- W: Overall width of the carrier tape
- P0: Pitch between successive cavity centers and sprocket hole
- P1: Pitch between successive cavity centers
- P2: Pitch between sprocket hole
- T: Tape material thickness
- D1: Reel Diameter
- W1: Reel Width

DIMENSIONS										(Unit: mm)
Reel	D1	W1								Material
	330	24.4								Hips
Tape	P0	P1	P2	W	A0	B0	K0	T	Pin 1 Quadrant	Material
	2	4	12	24	10.3	12.1	2.6	0.35	Q1	PC

All dimensions are nominal

**TOLL Package Information**



Symbol	Dimensions In Millimeters		
	Min.	Nom.	Max.
A	2.15	2.30	2.45
b	0.60	0.75	0.90
C	0.40	0.50	0.60
D	10.18	10.38	10.58
D1	3.15	3.3	3.45
E	9.70	9.90	10.10
E1	9.65	9.80	9.95
E2	7.90	--	9.15
E3	7.20	--	8.40
e	1.20 BSC		
F	1.05	1.20	1.35
H	11.45	11.70	11.95
H2	6.75	7.00	7.3
H3	3.00 BSC		
L	1.20	--	2.10
L1	0.50	0.75	0.90
L2	0.45	0.6	0.75
M	0.08 REF.		
$\beta$	8°	10°	12°