



0010836


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com




Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010836	N/A	Green

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=170 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	28.35	1.117	29.00	1.143	MAX	
ID (C)	15.78	0.622	15.00	0.591	MIN	
HT (B)	13.35	0.526	14.20	0.559	MAX	

Electrical Characeristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x0.5TSx120mm)			Initial Permeabili-ty	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
@25Mhz	60Ω	26°C	900	320 (4kA/m)	140	20.0	5.1	NZO	25.0
@100Mhz	100Ω	50%							

The Limit of Breakage					Temperature Rating	
Winding Length Per Turn		Wound Coil Dimensions (mm)			Curie Temp: -30°C-110°C	
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-
				Completely Full Window	HT	-
-	-	-	-		Max OD	-
-	-	-	-		Max HT	-
-	-	-	-	Surface Area (mm ²)		
-	-	-	-	Unwound Core		
-	-	-	-	40% Winding Factor		
					Notes:	

IMPEDANCE V.S FREQUENCY



Revision 10/8/2025

