





POLES	P/N	A	B
2	-2	3.96	7.92
3	-3	7.92	11.88
4	-4	11.88	15.84
5	-5	15.84	19.80
6	-6	19.80	23.76
7	-7	23.76	27.72
8	-8	27.72	31.68
9	-9	31.68	35.64
10	-10	35.64	39.60
11	-11	39.60	43.56
12	-12	43.56	47.52
13	-13	47.52	51.48
14	-14	51.48	55.44
15	-15	55.44	59.40



3D图示 (参考)



■ 技术参数(SPECIFICATIONS)

- ◆ 额定电压: 250V AC DC
Voltage rating: 250V AC DC
- ◆ 额定电流: 7.0A AC DC MAX.
Current rating: 7.0A AC DC MAX.
- ◆ 耐压值: 1500V AC/minute
Withstand voltage: 1500V AC/minute
- ◆ 绝缘电阻: 1000MΩ MIN
Insulation resistance: 1000MΩ MIN
- ◆ 接触电阻: 0.02Ω MAX(初始值)
Contact resistance: 0.02Ω MAX(Initial)
- ◆ 工作温度: -25°C~+85°C
Working Temperature: -25°C~+85°C
- ◆ 间距: 3.96 mm
Pitch: 3.96 mm

■ 材料(MATERIAL)

- ◆ 绝缘体: 尼龙66 UL94V-0
Insulator: PA66 UL94V-0
- ◆ 接触针: 黄铜镀锡
Contact PIN: Brass TIN-plating

DSND		SCALE: N/A	MODEL TYPE:		
DWN		VIEW: 	PART NO.: X9396WV-03-1-N0SN		
CHKD		UNIT: mm/in	DWG NO.:		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						