



0010789


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com




Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010789	N/A	No

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=120 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	19.00	0.749	20.90	0.823	MAX	
ID (C)	10.15	0.400	9.34	0.368	MIN	
HT (B)	28.54	1.124	29.68	1.169	MAX	

Electrical Characeristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x0.5TSx120mm)			Initial Permeabili-ty	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
			850	360 (1.6kA/m)	150	35.0	5.1	NZO	22.0
@25Mhz	250Ω	26°C							
@100Mhz	430Ω	50%							

The Limit of Breakage					Temperature Rating	
Winding Length Per Turn		Wound Coil Dimensions (mm)			Curie Temp: >160°C	
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-
				Completely Full Window	HT	-
-	-	-	-		Max OD	-
-	-	-	-		Max HT	-
-	-	-	-	Surface Area (mm ²)		
-	-	-	-	Unwound Core	-	
-	-	-	-	40% Winding Factor	-	
					Notes:	

IMPEDANCE V.S FREQUENCY



Revision 10/8/2025

