




General tolerances(mm)													0.1/10
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	$\frac{300}{10}$	/	300/10
IEC Standard			
Overvoltage Category/Pollution Degree	III/3	III/2	II/2
Rated Voltage(V)/Current(A)	160/10	200/10	400/10
Rate Impulse Voltage(KV)	2.5	2.5	2.5
Torque Tightening(N·m/Lb.in)	M2.0/0.2		
Wire Range(rigid and flexible)(mm ² /AWG)	26~16/1.0		
Pitch(mm)/Poles	3.81/N=02~24P		
Stripping length(mm)	5~6		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		



4	Screw	Steel	M2/Zn plated
3	Cage	Copper Alloy	M3/Ni Plated
2	Housing	PA66	UL94V-0
1	Pin header	Copper alloy	Sn plated
ITEM	NAME OF PART	MATERIAL	NOTES

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	制图 DRAWING	EMMA	料号 PART NO.	BX-DG28L-3.81-NP	版本 REV.	A
				审核 CHECK	EVA	品名 TITLE	DG380-3.81	页次 SHEET	1/1
				核准 APPROVAL	JADE	客户料号 CUTM.NO.			
				单位 UNITS	MM	比例 SCALE	1:1		