




RoHS

REVISIONS		
REV.	ECN NO.	DESCRIPTION
A1	2022/06/07	NEW DESIGN



Panel cut out







PCB layout

NOTE:

MAIN SPECIFICATION:

- Rated current: 250V AC, 15A
额定电流: 250V AC, 15A
- DIELECTRIC WITHSTAND VOLTAGE: 1500VAC
耐电压: 1500V MAX
- TEMPERATURE RANGE: -30 °C ~ 80 °C
使用温度: -30 °C ~ 80 °C
- CONTACT RESISTANCE: 30 MILLIONHM MAX
接触电阻: 30 MILLIONHM MAX
- INSULATION RESISTANCE: 1000 MEGOHMS MIN.
绝缘阻抗: 1000 MEGOHMS MIN.
- AFTER DURABILITY(5000CYCLES)
寿命 (5000次)



序号	料号	名称	材料	数量	镀层	备注
5	X3020-10-N3B	后盖	PA66 UL 94HB	1	黑色	
4	X3023-42-21G6	插针 1+ 2+	QSn6.5-0.1 t=0.4	2	Ag	
3	X3023-41-21G6	插针 1- 2-	QSn6.5-0.1 t=0.4	2	Ag	
2	X3020-81-41C8	锁片	SPCC t=0.4	1	CuSn	
1	X3023F-00-N3B	底座	PA66 UL 94HB	1	黑色	

X.±0.20	X.°±8°	Customer P/N:	浙江创都电子科技有限公司		
.X±0.15	.X°±5°	Customer REV.:			
.XX±0.07	.XX°±3°	PART NO.:	TITLE: Speakon,4pin立式四方座		
.XXX±0.05	.XXX°±1.5°	APPD:	DWG NO: XLR-E01F-ZJ-WDH-2.5		
UNITS: mm		CHKD:	SCALE	SHEET	REV.
		DRAW:	1:1	1/1	A1

