



MICRO SWITCH EV SERIES



■ FEATURES

- High applicability for general industrial equipment and home appliances
- High precision mechanism design offering durable acute operation and long life
- Heavy/Light operation force specifications
- Three Kinds of terminal available #187 quick connect/solder, #187 quick connect and #250 quick connect type
- RoHS Compliant
- Halogen Free series available

■ APPLICATIONS

- Home appliances
- Vending machines
- Amusement and communication equipment
- Office automation appliances
- General industrial machines

■ SPECIFICATIONS

1. ELECTRICAL

DESCRIPTION		TYPE	EV-11	EV-16	EV-21
Contact Rating:	AC 125V		11A 1/2HP	16A 1/2HP	21A 1/2HP
	AC 250V		11A 1/2HP	16A 1/2HP	21A 1/2HP
	DC 125V		0.6A	0.6A	0.6A
	DC 250V		0.3A	0.3A	0.3A
Contact Resistance: (Initial)			50mΩ Max.		
Insulation Resistance			100 MΩ Min. at 500 VDC		





2. CHARACTERISTICS

DESCRIPTION		TYPE	EV11	EV16	EV21
Mechanical Life (Cycles Operations)			50,000,000		
Electrical Life (Cycles Operations)			300,000	100,000	100,000
Ambient Temperature			-25°C to +80°C (without dew condensation)		
Ambient Humidity			Max. 85% RH		
Max. operating cycle rate	Mechanical		600 cycle/min.		
	Electrical		60 cycle/min.		
Allowable Operation speed			0.1 to 1,000 mm/sec (without lever)		
Dielectric Strength	Between non-continuous terminal		AC 1000Vrms		
	Between each terminal and other exposed metal parts		AC 2000Vrms		
	Between each terminal and ground		AC 2000Vrms		
Vibration Resistance (Without lever)			10 to 55 Hz amplitude of 1.5mm		
Shock Resistance (Without lever)			200m/s ² {20G}	300m/s ² {30G}	300m/s ² {30G}
Unit weight			Approx 6.5g		

■ PART NUMBERING SYSTEM

EV XX X X X X XX X

Blank: RoHS Compliant
H: Halogen Free series
XX: Special product number
00: Standard

Operation force: (Without lever)
1: 100 gf (EV11)
2: 200 gf (EV11, EV16)
3: 400 gf (EV11, EV16, EV21)

Actuator type:
0: Without lever
1: Short straight lever
2: Straight lever
3: Long straight lever
4: Simulated roller lever
5: Short roller lever
6: Roller lever

Terminal type:
1: #187 Quick connect/solder terminal (EV11, EV16)
2: #187 Quick connect terminal (EV11)
3: #250 Quick connect terminal (EV11, EV16, EV21)

Contact arrangement:
1: Bottom COM, SPST-NO (1a)
2: Bottom COM, SPST-NC (1b)
3: Bottom COM, SPDT (1c)
4: Side COM, SPST-NO (1a)
5: Side COM, SPST-NC (1b)
6: Side COM, SPDT (1c)


Rating current:
11: 11 Ampere
16: 16 Ampere
21: 21 Ampere

Series name:
EV: V type micro switch


Actuators		
0	Without lever	
1	Short straight lever	
2	Straight lever	
3	Long straight lever	
4	Simulated roller lever	
5	Short roller lever	
6	Roller lever	

Terminal type		
1	#187 Quick connect/solder terminal	
2	#187 Quick connect terminal	
3	#250 Quick connect terminal	


■ CIRCUIT DIMENSIONS



■ DIMENSIONS UNIT:mm(inch)




P/N: EV163112
 #187 Quick connect/solder terminal
 Short Straight lever




1.	Operating Force (OF)	200gf (1.96N) Max.
2.	Release Force (RF)	50gf (0.49N) Min.
3.	Pre-travel (PT)	1.6mm Max.
4.	Overtravel (OT)	0.8mm Min.
5.	Movement Differential (MD)	0.6mm Max.
6.	Operation Position (OP)	15.2 ± 0.5mm
7.	Free Position (FP)	

P/N: EV163122
 #187 Quick connect/solder terminal
 Straight lever




1.	Operating Force (OF)	125gf (1.23N) Max.
2.	Release Force (RF)	14gf (0.14N) Min.
3.	Pre-travel (PT)	4.0mm Max.
4.	Overtravel (OT)	1.6mm Min.
5.	Movement Differential (MD)	1.5mm Max.
6.	Operation Position (OP)	15.2 ± 1.2mm
7.	Free Position (FP)	


P/N: EV163132
 #187 Quick connect/solder terminal
 Long straight lever



P/N: EV163142
 #187 Quick connect/solder terminal
 Simulated roller lever



P/N: EV163152
 #187 Quick connect/solder terminal
 Short roller lever



P/N: EV163162
 #187 Quick connect/solder terminal
 Long roller lever

