



Description

The BUK966R5-60E can be used in various power switching circuit for system miniaturization and higher efficiency. The package form is TO-263, which accords with the RoHS standard.

General Features



$V_{DS} = 60V$ $I_D = 90A$

$R_{DS(ON)} < 7.5m\Omega @ V_{GS}=10V$

Application

Switching application

Power Management for Inverter Systems.



N-Channel MOSFET

Ordering Information

Product ID	Pack	Brand	Units/Tube)
BUK966R5-60E	TO-263(D2PAK)	HXY MOSFET	50

Absolute Maximum Ratings ($T_c=25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	Limit	Unit
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Drain Current-Continuous	90	A
$I_D (100^{\circ}C)$	Drain Current-Continuous($T_c=100^{\circ}C$)	51	A
I_{DM}	Pulsed Drain Current	320	A
P_D	Maximum Power Dissipation	83	W
E_{AS}	Repetitive Avalanche Energy	244	mJ
T_J, T_{STG}	Operating Junction and Storage Temperature Range	-55 To 150	$^{\circ}C$
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	1.5	$^{\circ}C/W$



Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	60	---	---	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{GS}=0V, V_{DS}=60V$	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0A$	---	---	± 100	nA
$V_{GS(th)}$	GATE-Source Threshold Voltage	$V_{GS}=V_{DS}, I_D=250\mu A$	2	2.8	4	V
$R_{DS(on)}$	Drain-Source On Resistance	$V_{GS}=10V, I_D=20A$	---	5.8	7.5	m Ω
C_{iss}	Input Capacitance	$V_{DS}=30V, V_{GS}=0V, f=1MHz$	---	4008	---	pF
C_{oss}	Output Capacitance		---	242	--	
C_{rss}	Reverse Transfer Capacitance		---	200	---	
$t_{d(on)}$	Turn-On Delay Time	$V_{DS}=30V, I_D=20A,$ $R_{ENG}=3\Omega, V_{GS}=10V$	---	18	---	ns
t_r	Rise Time		---	41	---	ns
$t_{d(off)}$	Turn-Off Delay Time		---	47	---	ns
t_f	Fall Time		---	28	---	ns
Q_g	Total Gate Charge	$V_{GS}=10V, V_{DS}=30V,$ $I_D=20A$	---	75	---	nc
Q_{gs}	Gate-Source Charge		---	18	---	nc
Q_{gd}	Gate-Drain "Miller" Charge		---	4.2	---	nc
V_{SD}	Diode Forward Voltage	$V_{GS}=0V, I_{SD}=20A$	---	---	1.2	V
I_S	Continuous Drain Current	$V_D=V_G=0V$	---	---	90	A
I_{SM}	Pulsed Drain Current		---	---	320	A
T_{rr}	Reverse Recovery Time	$I_F=20A, T_J=25^\circ\text{C}$	---	28	---	ns
Q_{rr}	Reverse Recovery Charge	$dI/dt=100A/\mu s$	---	52	---	nc

Notes:

1. $L=0.5mH, V_{DD}=30V$, Start $T_J=25^\circ\text{C}$.
2. Limited by maximum junction temperature.
3. Repetitive Rating: Pulse width limited by maximum junction temperature.



Typical Characteristics




Figure 1. Maximum Safe Operating Area




Figure 2. Maximum Power Dissipation vs. Case Temperature




Figure 3. Maximum Continuous Drain Current vs. Case Temperature




Figure 4. Typical output Characteristics




Figure 5. Maximum Effective Thermal Impedance, Junction to Case




Figure 6. Typical Transfer Characteristics




Figure 7. Typical Body Diode Transfer Characteristics




Figure 8. Drain-to-Source On Resistance vs Drain Current




Figure 9. Normalized On Resistance vs Junction Temperature




Figure 10. Normalized Threshold Voltage vs Junction Temperature




Figure 11. Normalized Breakdown Voltage vs Junction Temperature




Figure 12. Capacitance Characteristics





Figure 13. Typical Gate Charge vs Gate to Source Voltage



TO-263(D2PAK)Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.470	4.670	0.176	0.184
A1	0.000	0.150	0.000	0.006
B	1.120	1.420	0.044	0.056
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
c	0.310	0.530	0.012	0.021
c1	1.170	1.370	0.046	0.054
D	10.010	10.310	0.394	0.406
E	8.500	8.900	0.335	0.350
e	2.540 TYP.		0.100 TYP.	
e1	4.980	5.180	0.196	0.204
L	14.940	15.500	0.588	0.610
L1	4.950	5.450	0.195	0.215
L2	2.340	2.740	0.092	0.108
L3	1.300	1.700	0.051	0.067
Φ	0°	8°	0°	8°
V	5.600 REF.		0.220REF.	



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.