




REV	DESCRIPTION	DESIGN	DATE
A0			



Specifications:
 Contact resistance: $\leq 10\text{m}\Omega$
 Insulation resistance: $\geq 1000\text{M}\Omega$
 Rated voltage: 250V AC DC
 Rated current: 5.0A AC DC
 Withstand Voltage: 1000V AC/minute
 Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 Housing: LCP UL94V-0, BLACK
 Contacts: Brass/MATTE Sn-plated
 Solder Tabs: Brass/MATTE Sn-plated

PIN	DIM A	DIM B
2	3.00	9.65
3	6.00	12.65
4	9.00	15.65
5	12.00	18.65
6	15.00	21.65
7	18.00	24.65
8	21.00	27.65
*9	24.00	30.65
*10	27.00	33.65
*11	30.00	36.65
*12	33.00	39.65



浙江创都电子科技有限公司		TITLE: 3.0 Pitch Wafer 90° SMT	
		PART NO.: MX3.0-1 × *WT	
GENERAL TOLERANCE		APPD:	
X. ± 0.50	X. $\pm 5^{\circ}$	USE: CUSTOMER	
X.X ± 0.30	X.X $\pm 2^{\circ}$	CHKD:	
X.XX ± 0.20	X.XX $\pm 1^{\circ}$	DR:	
UNITS: mm		SCALE 1 : 1	SHEET 1 / 1