





REV.	ECN NO.	MODIFIED MARK	APPROVED
B			



NOTES:
ELECTRICAL:
1:RATED CURRENT: 1A Max.
2:RATED VOLTAGE: 12V DC.
3:CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING:100 MILLIOHMS Max.
4:INSULATION RESISTANCE: 100 MEGAOHMS Min.
5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1:INSERTION FORCE: 3N-30N.
2:WITHDRAWAL FORCE: 3N-30N.
3:DURRABILITY: 500 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -20°C TO 60°C.
MARK"▼"AS THE KEY CONTROL SIZE.
PIN POSITION AND SIZE OK IF FIT PCB BOARD

COLOR TABLE

CODE	A
COLOR	YELLOW
CODE	B
COLOR	WHITE
CODE	C
COLOR	RED



SCHEMATIC

⑧	COVER	1	ABS	BLACK	RoHS 2.0
⑦	TERMINAL-C	1	BRASS t=0.4	CuSn PLATED	
⑥	TERMINAL-B	1	BRASS t=0.35	CuSn PLATED	
⑤	TERMINAL-A	1	BRASS t=0.35	CuSn PLATED	
④	SOCKET-B	1	BRASS t=0.36	Au PLATED	
③	SOCKET-A	1	BRASS t=0.36	Au PLATED	
②	WASHER	3	ABS	SEE COLOR TABLE	
①	HOUSE	1	ABS	BLACK	
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK
ANGLE		±5°		浙江创都电子科技有限公司	
63 < L		±0.5			
16 < L ≤ 63		±0.4			
4 < L ≤ 16		±0.3			
L ≤ 4		±0.2		TITLE: AV-313-YWR	
TOL TABLE:		MAT'L: See table		DESIGN: F.	
		FINISH: See table		CHECKED:	
		Q'TY:/		APPROVED:	
		UNIT: mm		VIEW:	
		SCALE: 5:1		SHEET: 1/1	
		SIZE: A3		REV.: B	