THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2007
© COPYRIGHT 2007 BY - ALL RIGHTS RESERVED.

LOC	DIST
I	-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	23JUL2020	J.L	I.Y
	A1	ECN-23-193242	10JAN23	J.H	J.Z
	A2	ECN-24-247601	15JAN2024	J.Y	J.Z

DIMENSIONS FOR LEFT SIDE HOUSING COLOR BLACK - POS. 27-52 - ITEM 4





DIMENSIONS FOR RIGHT SIDE HOUSING COLOR GRAY - POS. 1-26 - ITEM 5





P.N. 2364137-1 AS SHOWN







PART LIST

ITEM	DESCRIPTION	MATERIAL	QUANTITY REQUIRED PER ASSEMBLY		
			2364137-1 REV. A COLOR BLACK	2364137-2 REV. A COLOR BLUE	2364137-3 REV. A COLOR GREY
1	LEVER	PA66 GF COLOR RED	1	1	1
2	COVER	PA66 GF COLOR BLACK	1		
3	COVER	PA66 GF COLOR BLUE		1	
4	COVER	PA66 GF COLOR GREY			1
5	REC. HOUSING 26 POS.	PBT GF COLOR BLACK	1	1	1
6	REC. HOUSING 26 POS.	PBT GF COLOR GRAY	1	1	1

NOTES

1) THE PRODUCT IS SUPPLIED WITH LEVER IN CLOSED POSITION

2) INTERFACE DRAWING: SEE SHEET 2 of 2

A2 3 NUMBER 26+26 CAVITIES SUITABLE FOR MICRO QUADLOCK SYSTEM FEMALE CONTACTS P.N. 5-928999-1 OR 5-2435200-1 WIRE RANGE 0.25-0.5 mm² AND P.N. 5-963715-1 OR 5-2435198-1 WIRE SECTION 0.75 mm²

4) NUMBER 1 SHELL + NUMBER 2 HOUSINGS ARE SUPPLIED IN KIT WITH EQUIVALENT NUMBER OF PIECES FOR EACH COMPONENT IN A BOX

2364137 IS SZHOU VERSION OF 284972 BOTH HAVE THE SIMILAR PERFORMANCE.	
ORIGINAL P/N	NEW LOCAL P/N
284972-1	2364137-1
284972-2	2364137-2
284972-3	2364137-3

MECHANICAL CODING DIMENSIONS P.N. 2364137-1 - COLOR BLACK



MECHANICAL CODING DIMENSIONS P.N. 2364137-2 - COLOR BLUE



MECHANICAL CODING DIMENSIONS P.N. 2364137-3 - COLOR GREY



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.3
1 PLC ±0.3
2 PLC ±0.3
3 PLC ±:
4 PLC ±:
ANGLES ±2°

MATERIAL: SEE TABLE (VEDI TABELLA)

FINISH: SEE TABLE (VEDI TABELLA)

DWN	J.YANG	15JAN2024
CHK	J.LEE	15JAN2024
APVD	J.ZONG	15JAN2024
PRODUCT SPEC	108-20258	
APPLICATION SPEC	-	
WEIGHT	-	

TE Connectivity

NAME: KIT ASS'Y FOR 52 (26+26) POSITIONS MQS FEMALE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2364137	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 2 | REV A2

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2007
© COPYRIGHT 2007 BY - ALL RIGHTS RESERVED.

LOC	DIST
1	-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:

5) HOUSING MATERIAL: PA 66 (OR PBT) 10% G.F. MIN.

6) CONTACT MATERIAL: CuFe2 (OR BRASS) TIN PLATED 2-4µm THK.



SECTION A-A



DETAIL A
SCALE 20:1



SECTION B-B

INTERFACE DRAWING

	POLARIZATION KEY DETAIL	PLUG CONNECTOR
CODE 1	 SEE BESIDE	2364137-1 (BLACK)
CODE 2		2364137-2 (BLUE)
CODE 3		2364137-3 (GREY)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.3
1 PLC ±0.3
2 PLC ±0.3
3 PLC ±-
4 PLC ±-
ANGLES ±2°

MATERIAL

FINISH

DWN	J.YANG	15JAN2024
CHK	J.LEE	15JAN2024
APVD	J.ZONG	15JAN2024
PRODUCT SPEC	108-20258	
APPLICATION SPEC	-	
WEIGHT	-	

TE Connectivity

NAME KIT ASS'Y FOR 52 (26+26) POSITIONS MQS FEMALE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2364137	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 2 OF 2 | REV A2