

Dual Band 2.4/5GHz 2x2 802.11ac Wave 1 MiniPCle WiFi Module Designed for Dual Band Wireless Access Points

Model: WLE600VX-I



KEY FEATURES

- Qualcomm Atheros QCA9892
- 2.4GHz, 2x2 MIMO OFDM Technology, up to 400Mbps physical data rate
- 5GHz, 2x2 MIMO OFDM Technology, up to 866.7Mbps physical data rate
- Dual Band 2.4/5GHz 2x2 WiFi 5 (802.11ac Wave 1)
- MiniPCle interface with PCIe 1.1
- Industrial Grade Chipset
- Supports Spatial Multiplexing, Cyclic-Delay Diversity (CDD), Low-Density Parity Check (LDPC) Codes, Maximal Ratio Combining (MRC), Space Time Block Code (STBC)
- Supports IEEE 802.11d, e, h, i, j, k, r, v time stamp, and w standards
- Supports Dynamic Frequency Selection (DFS)
- Cards are individually calibrated for Quality Assurance
- Supports 4.9GHz operation

Specifications

Chipset	Qualcomm Atheros QCA9892 'Peregrine' Series
Reference Design	Qualcomm Atheros XB140
Host Interface	MiniPCle interface with PCIe 1.1
Operating Voltage	3.3V
Power Consumption	3.5W (Max)
Wireless	2.4GHz 802.11b/g/n, max 21dBm per chain 5GHz 802.11a/n/ac, max 20dBm per chain 2x U.FL Connectors
Frequency Range	2.412~2.472GHz, 4.920~5.825GHz, selectable dual band
Modulation Techniques	OFDM: BPSK, QPSK, DBPSK, DQPSK, CCK, 16-QAM, 64-QAM, 256-QAM
Channel Spectrum Widths for WLAN	Supports 20/40MHz at 2.4GHz, Supports 20/40/80MHz at 5GHz
ESD Sensitivity	Class 1C
Supported Operating System	Supported by CompexWRT with Qualcomm Atheros reference wireless drivers or OpenWRT/LEDE with ath10k wireless drivers, on WPJ344, WPJ558, WPJ563, WPJ564, WPQ864, and WPQ865.
Certification	FCC, CE Certified, REACH and RoHS Compliance
Environmental Temperature (Industrial Grade)	Operating: -40°C to 70°C*, Storage: -40°C to 90°C *The wireless module can operate up to 90°C. For long term reliability, it is recommended that a 20°C safety margin be maintained.
Environmental Humidity, Non-Condensing	Operating: 5% to 95%, Storage: Max. 90%
Dimensions (W x H x D) in mm	29.85 × 50.8 × 4.5

*Configurations are subject to change without notifications.

RF Performance Table for 2.4GHz

	Data Rate	TX Power (per chain)	TX Power (2 chains)	Tolerance
2.4GHz 802.11b	1Mbps	20dBm	23dBm	±2dB
	2Mbps	20dBm	23dBm	±2dB
	5.5Mbps	20dBm	23dBm	±2dB
	11Mbps	20dBm	23dBm	±2dB
2.4GHz 802.11g	6Mbps	21dBm	24dBm	±2dB
	9Mbps	21dBm	24dBm	±2dB
	12Mbps	21dBm	24dBm	±2dB
	18Mbps	21dBm	24dBm	±2dB
	24Mbps	21dBm	24dBm	±2dB
	36Mbps	20dBm	23dBm	±2dB
	48Mbps	19dBm	22dBm	±2dB
	54Mbps	18dBm	21dBm	±2dB
2.4GHz 802.11n HT20	MCS 0	21dBm	24dBm	±2dB
	MCS 1	21dBm	24dBm	±2dB
	MCS 2	21dBm	24dBm	±2dB
	MCS 3	20dBm	23dBm	±2dB
	MCS 4	20dBm	23dBm	±2dB
	MCS 5	20dBm	23dBm	±2dB
	MCS 6	18dBm	21dBm	±2dB
	MCS 7	16dBm	19dBm	±2dB
2.4GHz 802.11n HT40	MCS 0	20dBm	23dBm	±2dB
	MCS 1	20dBm	23dBm	±2dB
	MCS 2	20dBm	23dBm	±2dB
	MCS 3	19dBm	22dBm	±2dB
	MCS 4	19dBm	22dBm	±2dB
	MCS 5	19dBm	22dBm	±2dB
	MCS 6	18dBm	21dBm	±2dB
	MCS 7	16dBm	19dBm	±2dB

	Data Rate	RX Specifications Sensitivity	Tolerance
2.4GHz 802.11b	1Mbps	-95dBm	±2dB
	2Mbps	-94dBm	±2dB
	5.5Mbps	-92dBm	±2dB
	11Mbps	-90dBm	±2dB
2.4GHz 802.11g	6Mbps	-94dBm	±2dB
	9Mbps	-93dBm	±2dB
	12Mbps	-92dBm	±2dB
	18Mbps	-90dBm	±2dB
	24Mbps	-88dBm	±2dB
	36Mbps	-85dBm	±2dB
	48Mbps	-81dBm	±2dB
	54Mbps	-80dBm	±2dB
2.4GHz 802.11n HT20	MCS 0	-93dBm	±2dB
	MCS 1	-91dBm	±2dB
	MCS 2	-89dBm	±2dB
	MCS 3	-84dBm	±2dB
	MCS 4	-83dBm	±2dB
	MCS 5	-78dBm	±2dB
	MCS 6	-78dBm	±2dB
	MCS 7	-76dBm	±2dB
2.4GHz 802.11n HT40	MCS 0	-92dBm	±2dB
	MCS 1	-88dBm	±2dB
	MCS 2	-85dBm	±2dB
	MCS 3	-82dBm	±2dB
	MCS 4	-79dBm	±2dB
	MCS 5	-75dBm	±2dB
	MCS 6	-75dBm	±2dB
	MCS 7	-73dBm	±2dB

RF Performance Table for 5GHz


	Data Rate	TX Power (per chain)	TX Power (2 chains)	Tolerance
5GHz 802.11a	6Mbps	20dBm	23dBm	±2dB
	9Mbps	20dBm	23dBm	±2dB
	12Mbps	20dBm	23dBm	±2dB
	18Mbps	20dBm	23dBm	±2dB
	24Mbps	20dBm	23dBm	±2dB
	36Mbps	18dBm	21dBm	±2dB
	48Mbps	16dBm	19dBm	±2dB
	54Mbps	15dBm	18dBm	±2dB
5GHz 802.11n/ac VHT20	MCS 0	19dBm	22dBm	±2dB
	MCS 1	19dBm	22dBm	±2dB
	MCS 2	19dBm	22dBm	±2dB
	MCS 3	18dBm	21dBm	±2dB
	MCS 4	18dBm	21dBm	±2dB
	MCS 5	17dBm	20dBm	±2dB
	MCS 6	16dBm	19dBm	±2dB
	MCS 7	14dBm	17dBm	±2dB
5GHz 802.11n/ac VHT40	MCS 8	13dBm	16dBm	±2dB
	MCS 0	18dBm	21dBm	±2dB
	MCS 1	18dBm	21dBm	±2dB
	MCS 2	18dBm	21dBm	±2dB
	MCS 3	17dBm	20dBm	±2dB
	MCS 4	17dBm	20dBm	±2dB
	MCS 5	16dBm	19dBm	±2dB
	MCS 6	15dBm	18dBm	±2dB
5GHz 802.11n/ac VHT80	MCS 7	14dBm	17dBm	±2dB
	MCS 8	13dBm	16dBm	±2dB
	MCS 9	13dBm	16dBm	±2dB
	MCS 0	18dBm	21dBm	±2dB
	MCS 1	18dBm	21dBm	±2dB
	MCS 2	18dBm	21dBm	±2dB
	MCS 3	17dBm	20dBm	±2dB
	MCS 4	17dBm	20dBm	±2dB
5GHz 802.11n/ac VHT80	MCS 5	16dBm	19dBm	±2dB
	MCS 6	15dBm	18dBm	±2dB
	MCS 7	14dBm	17dBm	±2dB
	MCS 8	13dBm	16dBm	±2dB
	MCS 9	13dBm	16dBm	±2dB

	Data Rate	RX Specifications Sensitivity	Tolerance
5GHz 802.11a	6Mbps	-94dBm	±2dB
	9Mbps	-94dBm	±2dB
	12Mbps	-92dBm	±2dB
	18Mbps	-90dBm	±2dB
	24Mbps	-86dBm	±2dB
	36Mbps	-84dBm	±2dB
	48Mbps	-81dBm	±2dB
	54Mbps	-80dBm	±2dB
5GHz 802.11n/ac VHT20	MCS 0	-93dBm	±2dB
	MCS 1	-90dBm	±2dB
	MCS 2	-87dBm	±2dB
	MCS 3	-83dBm	±2dB
	MCS 4	-80dBm	±2dB
	MCS 5	-77dBm	±2dB
	MCS 6	-74dBm	±2dB
	MCS 7	-73dBm	±2dB
5GHz 802.11n/ac VHT40	MCS 8	-71dBm	±2dB
	MCS 0	-90dBm	±2dB
	MCS 1	-88dBm	±2dB
	MCS 2	-85dBm	±2dB
	MCS 3	-82dBm	±2dB
	MCS 4	-79dBm	±2dB
	MCS 5	-75dBm	±2dB
	MCS 6	-73dBm	±2dB
5GHz 802.11n/ac VHT80	MCS 7	-73dBm	±2dB
	MCS 8	-69dBm	±2dB
	MCS 9	-66dBm	±2dB
	MCS 0	-88dBm	±2dB
	MCS 1	-86dBm	±2dB
	MCS 2	-84dBm	±2dB
	MCS 3	-81dBm	±2dB
	MCS 4	-77dBm	±2dB
5GHz 802.11n/ac VHT80	MCS 5	-74dBm	±2dB
	MCS 6	-73dBm	±2dB
	MCS 7	-70dBm	±2dB
	MCS 8	-67dBm	±2dB
	MCS 9	-65dBm	±2dB

Component Map



Mechanical Dimensions



Ordering Configuration

Item Code	Model	Description
WLE600VX 7BA000S-I	WLE600VX-I	Industrial Grade 2x2 802.11a/b/g/n/ac 2.4GHz/5GHz miniPCIe card