


180V MOSvp[®] Voltage Regulator / Overvoltage Protector
General Features

- Typical Output Voltage: 16.5V @ I_{OUT}=1mA
- Wide Input Voltage Range: 0 to 180V
- High-speed Transient Response
- Excellent Temperature Characteristics
- High Reliability
- RoHS Compliant
- Halogen-free Available

V _{IN}	R _{ON(Typ.)}	V _{OUT(Typ.)}
180V	7 Ω	16.5V

Applications

- Industrial Control
- Automotive
- Domestic Appliances
- Photovoltaic
- Overvoltage Protection
- Overcurrent Protection
- Voltage Source
- Current Source


Ordering Information

Part Number	Package	Marking	Remark
AKZ16V15R	SOT-23	16V15R	Halogen Free
AKX16V15R	SOT-89	16V15R	Halogen Free
AKS16V15R	SOT-223	16V15R	Halogen Free

Absolute Maximum Ratings
T_A =25°C unless otherwise specified

Symbol	Parameter	AKZ16V15R	AKX16V15R	AKS16V15R	Unit
V _{IN}	Input Voltage to GND ^[1]	180			V
I _{OUT}	Continuous V _{OUT} Current ^[1]	30	50	70	mA
P _D	Power Dissipation ^[2]	0.5	1.0	1.5	W
T _L	Soldering Temperature Distance of 1.6mm from case for 10s	300			°C
T _J & T _{STG}	Operating and Storage Temperature Range	-55 to 150			

Warning: Stresses exceeding the "Absolute Maximum Ratings" may cause permanent damage to the device.

Thermal Characteristics

Symbol	Parameter	AKZ16V15R	AKX16V15R	AKS16V15R	Unit
R _{θJA}	Thermal Resistance, Junction-to-Ambient	250	125	83	K/W

Typical Application Circuits

The AKZ16V15R/AKX16V15R/AKS16V15R series are high-voltage integrated regulators (HVIR) developed by ARK using MOSovp® technology. This series of products integrates temperature compensation design, with excellent temperature characteristics; The internal integrated N-channel depletion MOSFET has extremely fast response speed, which can effectively suppress circuit surges and transient interference, reduce output voltage ripple, ensure stable output voltage, and only have very low static current.

AKZ16V15R/AKX16V15R/AKS16V15R series products have internal integrated depletion mode MOSFET, with fast response speed, that can effectively suppress circuit surge and transient disturbance, and provide reliable over-voltage protection for load circuit. Typical application circuit is shown in Figure 1:




Figure 1. Typical application schemes of HVIR series products for overvoltage protection

This series of products can withstand voltage up to 180V, which is very suitable for the application of input power supply with a wide voltage range. It can be directly used as a regulator to convert high voltage into stable low voltage, and supply power to MCU and other loads. Typical application circuit schemes and circuit voltage regulation parameters are shown in fig. 2 and fig. 3:




Figure 2. Typical application scheme for stabilizing power supply




Figure 3. Circuit test results

In QC2.0/3.0 and Type-C/PD charger circuits, the AKZ16V15R/AKX16V15R/AKS16V15R is used as a high-voltage linear regulator to supply power to the PWM IC, and its allowable input voltage is up to 180V, which effectively simplifies the circuit. The typical application circuit is shown in Figure 4:




Figure 4. A typical application scheme for AKZ16V15R to supply power for PWM IC

Electrical Characteristics
 $T_A = 25^\circ\text{C}$ unless otherwise specified

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
V_{IN}	Input Voltage to GND	--	--	180	V	$T_J = -40^\circ\text{C}$ to $+150^\circ\text{C}$
V_{OUT}	Output Voltage ($V_{IN} < V_{CLAMP}$) ^[3]	--	V_{IN}	--	V	$T_J = -40^\circ\text{C}$ to $+150^\circ\text{C}$
	Output Voltage ($V_{IN} > V_{OUT}$)	--	--	20	V	$V_{IN} = 25$ to 180 V, $I_{OUT} = 0$ μA
		--	17	--	V	$V_{IN} = 25$ to 180 V, $I_{OUT} = 10$ to 100 μA
		--	16.5	--	V	$V_{IN} = 25$ to 180 V, $I_{OUT} = 0.1$ to 1 mA
		13	16	--	V	$V_{IN} = 25$ to 60 V, $I_{OUT} = 3$ to 10 mA
R_{ON}	Static On-state Resistance ^[4]	--	7	25	Ω	$V_{OUT} = V_{GND}$ $I_{OUT} = 100\text{mA}$
I_{GND}	Quiescent Current	--	--	20	μA	$V_{IN} = 10$ to 180 V, $I_{OUT} = 0$ mA

NOTE:

[1] Cannot exceed the Power Dissipation of the device.

[2] $T_C = +25^\circ\text{C}$.

[3] The input voltage is lower than the clamp voltage value, the internal depletion MOSFET operate in a linear resistance region, and the output voltage is approximately equal to the input voltage value.

[4] Pulse width $\leq 380\mu\text{s}$, duty cycle $\leq 2\%$.

Typical Characteristics

Figure 5. Output Voltage(Vout) vs. Ambient Temperature




Figure 6. Output Voltage(Vout) vs. Junction Temperature




Figure 7. Output Voltage vs. Input Voltage






Figure 8. Output Voltage vs. Load Current







Package Dimensions


SOT-23



SOT-89



SOT-223





Published by

ARK Microelectronics Co., Ltd.

Add: D26, UESTC National Science Park, No. 1 Shuangxing Avenue, Chengdu, Sichuan

Tel: +86 (028) 8523-2215 Email: sales@ark-micro.com Website: www.ark-micro.com

All Rights Reserved.

Disclaimers

ARK Microelectronics Co., Ltd. reserves the right to make change without notice in order to improve reliability, function or design and to discontinue any product or service without notice. Customers should obtain the latest relevant information before orders and should verify that such information is current and complete. All products are sold subject to ARK Microelectronics Co., Ltd.'s terms and conditions supplied at the time of order acknowledgement.

ARK Microelectronics Co., Ltd. warrants performance of its hardware products to the specifications at the time of sale, Testing, reliability and quality control are used to the extent ARK Microelectronics Co., Ltd deems necessary to support this warrantee. Except where agreed upon by contractual agreement, testing of all parameters of each product is not necessary performed.

ARK Microelectronics Co., Ltd. does not assume any liability arising from the use of any product or circuit designs described herein. Customers are responsible for their products and applications using ARK Microelectronics Co., Ltd.'s components. To minimize risk, customers must provide adequate design and operating safeguards.

ARK Microelectronics Co., Ltd. does not warrant or convey any license either expressed or implied under its patent rights, nor the rights of others. Reproduction of information in ARK Microelectronics Co., Ltd.'s data sheets or data books is permissible only if reproduction is without modification or alteration. Reproduction of this information with any alteration is an unfair and deceptive business practice. ARK Microelectronics Co., Ltd. is not responsible or liable for such altered documentation.

Resale of ARK Microelectronics Co., Ltd.'s products with statements different from or beyond the parameters stated by ARK Microelectronics Co., Ltd. for the product or service voids all express or implied warranties for the associated ARK Microelectronics Co., Ltd.'s product or service and is unfair and deceptive business practice. ARK Microelectronics Co., Ltd. is not responsible or liable for any such statements.

Life Support Policy:

ARK Microelectronics Co., Ltd.'s products are not authorized for use as critical components in life support devices or systems without the express written approval of ARK Microelectronics Co., Ltd.

As used herein:

1. Life support devices or systems are devices or systems which:
 - a. Are intended for surgical implant into the human body,
 - b. Support or sustain life, or
 - c. When used in accordance with instructions provided in their labeling, whose failure to perform can be reasonably expected to result in significant injury to the patient.
 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to:
 - a. Cause the failure of the life support device or system, or
 - b. Affect its safety or effectiveness.
-