



QNHCHIP

QNM50P03AY

Product Specification

QNM50P03AY

30V P-Channel MOSFET





FEATURES

- -30V, -40A
 $R_{DS(ON)}$ Typ = 7.4m Ω @ $V_{GS} = -10V$
 $R_{DS(ON)}$ Typ = 13.5m Ω @ $V_{GS} = -4.5V$
- Advanced Trench Technology
- Excellent $R_{DS(ON)}$ and Low Gate Charge
- Lead Free
- 100% UIS TESTED
- 100% ΔV_d s TESTED

Applications

- PWM Applications
- Load Switch
- Power Management

Pin Description



NO.	Symbol	Description
1	S	SOURCE
2	S	SOURCE
3	S	SOURCE
4	G	GATE
5	D	DRAIN
6	D	DRAIN
7	D	DRAIN
8	D	DRAIN



Absolute Maximum Ratings

(@ $T_C = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Units	
V_{DS}	Drain-to-Source Voltage	-30	V	
V_{GS}	Gate-to-Source Voltage	± 20	V	
I_D	Continuous Drain Current	$T_C = 25^\circ\text{C}$	-40	A
		$T_C = 100^\circ\text{C}$	-24	
I_{DM}	Pulsed Drain Current ⁽¹⁾	-160	A	
E_{AS}	Single Pulsed Avalanche Energy ⁽²⁾	56	mJ	
P_D	Power Dissipation	$T_C = 25^\circ\text{C}$	26	W
$R_{\theta JC}$	Thermal Resistance, Junction to Case	4.8	$^\circ\text{C}/\text{W}$	
T_J, T_{STG}	Junction & Storage Temperature Range	-55 to 150	$^\circ\text{C}$	



Electrical Characteristics

($T_J = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Off Characteristics						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$I_D = -250\mu\text{A}, V_{GS} = 0\text{V}$	-30	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = -30\text{V}, V_{GS} = 0\text{V}$	-	-	1.0	μA
I_{GSS}	Gate-Body Leakage Current	$V_{DS} = 0\text{V}, V_{GS} = \pm 20\text{V}$	-	-	± 100	nA
On Characteristics						
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\mu\text{A}$	-1	-1.6	-2.2	V
$R_{DS(ON)}$	Static Drain-Source ON-Resistance ⁽³⁾	$V_{GS} = -10\text{V}, I_D = -15\text{A}$	-	7.4	9.6	$\text{m}\Omega$
		$V_{GS} = -4.5\text{V}, I_D = 10\text{A}$	-	13.5	15.3	$\text{m}\Omega$
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{GS} = 0\text{V}, V_{DS} = -15\text{V}, f = 1\text{MHz}$	-	1390	-	pF
C_{oss}	Output Capacitance		-	251	-	pF
C_{rss}	Reverse Transfer Capacitance		-	217	-	pF
Q_g	Total Gate Charge	$V_{GS} = 0 \sim -10\text{V}, V_{DS} = -15\text{V}, I_D = -20\text{A}$	-	25	-	nC
Q_{gs}	Gate Source Charge		-	4	-	nC
Q_{gd}	Gate Drain ("Miller") Charge		-	5.5	-	nC
Switching Characteristics						
$t_{d(on)}$	Turn-On Delay Time	$V_{GS} = -10\text{V}, V_{DD} = -15\text{V}, I_D = -20\text{A}, R_{GEN} = 3\Omega$	-	11	-	ns
t_r	Turn-On Rise Time		-	17	-	ns
$t_{d(off)}$	Turn-Off Delay Time		-	60	-	ns
t_f	Turn-Off Fall Time		-	45	-	ns
Drain-Source Diode Characteristics and Max Ratings						
I_S	Maximum Continuous Drain to Source Diode Forward Current		-	-	-40	A
I_{SM}	Maximum Pulsed Drain to Source Diode Forward Current		-	-	-160	A
V_{SD}	Drain to Source Diode Forward Voltage	$V_{GS} = 0\text{V}, I_S = -15\text{A}$	-	-	-1.2	V
t_{rr}	Body Diode Reverse Recovery Time	$I_F = -20\text{A}, di/dt = 100\text{A}/\mu\text{s}$	-	15	-	ns
Q_{rr}	Body Diode Reverse Recovery Charge		-	6	-	nC

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature.
2. E_{AS} condition: Starting $T_J = 25^\circ\text{C}$, $V_{DD} = -15\text{V}$, $V_G = -10\text{V}$, $R_G = 25\Omega$, $L = 0.5\text{mH}$, $I_{AS} = -15\text{A}$
3. Pulse Test: Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 0.5\%$.



Test Circuit-P

Figure 1: Gate Charge Test Circuit & Waveform




Figure 2: Resistive Switching Test Circuit & Waveform




Figure 3: Unclamped Inductive Switching Test Circuit & Waveform






Figure 4: Diode Recovery Test Circuit & Waveform






Package Mechanical Data(PDFN 3x3-8)



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.650	0.850	0.026	0.033
A1	0.152 REF.		0.006 REF.	
A2	0~0.05		0~0.002	
D	2.900	3.100	0.114	0.122
D1	2.300	2.600	0.091	0.102
E	2.900	3.100	0.114	0.122
E1	3.150	3.450	0.124	0.136
E2	1.535	1.935	0.060	0.076
b	0.200	0.400	0.008	0.016
e	0.550	0.750	0.022	0.030
L	0.300	0.500	0.012	0.020
L1	0.180	0.480	0.007	0.019
L2	0~0.100		0~0.004	
L3	0~0.100		0~0.004	
H	0.315	0.515	0.012	0.020
θ	9°	13°	9°	13°



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Ordering information

Order Code	Package	$V_{DS}(V)$	$I_D(A)$	$R_{DS(ON)}(m\Omega)$	
QNM50P03AY	PDFN 3x3-8	-30	-40	$V_{GS}=-10V$	7.4
				$V_{GS}=-4.5V$	13.5