

## PTC Thermistor Inrush Current Limiter

# PTCL

60~1000  $\Omega$   $R_{25}$

500~1000  $V_{DC}$   $V_{linkmax}$

350~700  $V_{rms}$   $V_{max}$

1.45~2.3 J/K  $C_{th}$



### Applications

AC/DC and DC/DC converters / Load dump and DC-Link circuits  
OBC / Battery charging equipment / Motor drives

## Outstanding High-Voltage Capability, High Stability and Reliability

### Wide working temperature range



### Introduction

The PTCL series is a high-performance PTC thermistor inrush current limiter introduced by C&B Electronics. This series is specifically designed to handle transient current surges in high-voltage power conversion and new energy systems, serving as a core component for efficient and reliable pre-charge protection.

The PTCL series utilizes the positive temperature coefficient (PTC) characteristics of ceramic materials to limit inrush currents through its initial resistance at the moment of circuit startup. When an abnormal overcurrent causes the component's temperature to reach the Curie temperature ( $+140\pm 10^{\circ}\text{C}$ ), its resistance increases exponentially, thereby restricting the current to an extremely low level and effectively protecting downstream capacitors and power devices from damage.

**Outstanding High-Voltage Capability:** With  $V_{\text{linkmax}}$  ranging from  $500V_{\text{DC}}$  to  $1000V_{\text{DC}}$ , it easily meets the requirements of high-voltage power battery systems and industrial power environments.

**Diverse Specification Options:**  $R_{25}$  values range from  $60\Omega$  to  $1000\Omega$ , combined with a high heat capacity ( $C_{\text{th}}$ ) of up to  $2.3\text{J/K}$ , providing precise matching solutions for circuit designs with various power densities.

If you have any customization needs beyond this document, feel free to contact us at the following email address: [resi@cbeureka.com](mailto:resi@cbeureka.com)



## Electrical Parameters


Size	$R_{25}$ <sup>[1]</sup> ( $\Omega$ )	$R_{25}$ TOL. (%)	TC. <sup>[2]</sup> ( $^{\circ}\text{C}$ )	$V_{\text{max}}$ ( $V_{\text{rms}}$ )	$V_{\text{linkmax}}$ ( $V_{\text{DC}}$ )	$C_{\text{th}}$ (J/K)	$\tau_{\text{th}}$ (s)	Operating Temp. Range ( $^{\circ}\text{C}$ )
PTCL0850N1K00Y5	1000	30	$140\pm 10$	$600V_{\text{AC}}$	850	$\approx 1.45$	$\approx 130$	-40~+105
PTCL0500N60R0Y5	60	30	$140\pm 10$	$350V_{\text{AC}}$	500	$\approx 1.45$	$\approx 130$	-40~+105
PTCL0625N120RY5	120	30	$140\pm 10$	$440V_{\text{AC}}$	625	$\approx 1.45$	$\approx 130$	-40~+105
PTCL0680N250RY5	250	30	$140\pm 10$	$480V_{\text{AC}}$	680	$\approx 1.45$	$\approx 130$	-40~+105
PTCL0800N500RY5	500	30	$140\pm 10$	$560V_{\text{AC}}$	800	$\approx 1.45$	$\approx 130$	-40~+150
PTCL0625N60R0Y5	60	30	$140\pm 10$	$440V_{\text{AC}}$	625	$\approx 2.3$	$\approx 155$	-40~+150
PTCL0650N120RY5	120	30	$140\pm 10$	$460V_{\text{AC}}$	650	$\approx 2.3$	$\approx 155$	-40~+150
PTCL0850N250RY5	250	30	$140\pm 10$	$600V_{\text{AC}}$	850	$\approx 2.3$	$\approx 155$	-40~+150
PTCL1000N500RY5	500	30	$140\pm 10$	$700V_{\text{AC}}$	1000	$\approx 2.3$	$\approx 155$	-40~+150

[1], Testing voltage: 1.5VDC

[2], Curie Temperature: The resistance at TC is twice of  $R_{25}$

## Dimensions


Unit: mm



Size	W	L	H	D	a	t
PTCL0850N1K00Y5 PTCL0500N60R0Y5 PTCL0625N120RY5 PTCL0680N250RY5 PTCL0800N500RY5	14.0 Max	8.0 Max	17.0 Max	18.0 Max	7.5±1.0	0.8±0.1
PTCL0625N60R0Y5 PTCL0650N120RY5 PTCL0850N250RY5 PTCL1000N500RY5	17.0 Max	8.0 Max	21.0 Max	18.0 Max	7.5±1.0	0.8±0.1

## Selection Table

Selection Example: PTCL0850N250RY5 (PTCL 850V<sub>DC</sub> ±30% 250Ω Code)




Series	Max. Link voltage	Tolerance	Resistance	Code
PTCL	0500=500V <sub>DC</sub> 0625=625V <sub>DC</sub> 0650=650V <sub>DC</sub> 0680=680V <sub>DC</sub> 0800=800V <sub>DC</sub> 0850=850V <sub>DC</sub> 1000=1000V <sub>DC</sub>	N=±30%	60R=60Ω 120R=120Ω 250R=250Ω 500R=500Ω 1K00=1000Ω	Y5=Code

## Performance

Test	Test Method	Typical
Strength of Terminal	4.9N applied the terminals, 10s	No damage
Terminal Bending strength	Posistor is held so that it is perpendicular to the lead wire with the force of 2.45N in the axial direction of the lead wire. The lead wire is slowly bent 90° and returned. Then it's slowly bent in the opposite direction and returned to original state.	No come off
Solder ability	Dip each lead into 230±5°C solder tub for 3±1second with the 5mm lead length remaining down from the bottom of the body of the sample. Check the surface covered with solder	Min.90% terminal is covered with solder.
Vibration Test	The change rate of vibration frequency shall be so selected that the frequency should increase from 10 to 55 Hz and return again to 10Hz for 1 minute with 3.0mm of vibration width. Such vibration cycle shall be repeated at X、Y and Z directions for each 1 hour	No visible damage; ΔR≤20%
Insulation Resistance	Under normal temperature and humidity conditions, connect the two electrodes of the product as the positive electrode, and wrap the envelope with aluminum foil as the negative electrode. There should be a gap of 2-2.5mm between the edge of the aluminum foil and the lead wire. Measure with a DC500V megger. Under normal temperature and humidity, the insulation resistance is more than 100M Ω.	>100MΩ
Electrical endurance, cycling	Room temperature, Maximum Voltage, applied energy <math>< C_{th} \times (T_{ref} - TA)</math>, 1000cycles	ΔR≤25%
High temperature test	Storage at Vmax, 105°C, 1000h	ΔR≤25%
Humidity State characteristics	40±2°C, 90-95%RH, 1000h	ΔR≤25%
Climatic sequence	+125°C 16h, -40°C 2h, 5cycles	ΔR≤25%

## R-T CURVE



## Attention

1. Do not apply abnormal voltage/current exceeding the specified maximum value. Because they may deteriorate or destroy PTC element
2. Use this product within the specified temperature. A higher temperature may deteriorate the characteristic or material
3. When this product is operated, temperature of some area may be over 100°C to 160°C. Please make sure that surrounding parts and inserting material can withstand the temperature. If the surrounding part and material is kept under such condition, they may be deteriorated or may produce harmful gas(Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>x</sub>, NO<sub>x</sub> etc.).And, such harmful gas may deteriorate the element
4. The resin coating of this product is not for insulating purpose. Keep an adequate insulating distance to surrounding components
5. "This product does not have waterproof construction. A splashed water may cause failure mode such as decline of characteristic or current leak. So, Do NOT apply cleaning to immerse it into water or any solvent."
6. If you coat this product by resin, please evaluate the quality of this product before you use it. The stress of force which is caused by coating materials or heat cycles may cause failure mode such as deterioration of characteristic or current leak in worst case.
7. This product is using the solder of 220+/-5°C of melting points, in order to connect ceramics with a lead wire. Do not heat up a terminal area of this product over 180°C.
8. The ceramic element of this product is fragile, and care must be taken not to load an excessive pressure or not to give a shock at handling. Such forces may cause cracking or chipping.
9. Do not apply an excessive force to the lead. Otherwise, it may cause break off the junction between lead and element, or may crack element. Therefore, hold of element side lead wire is recommended when lead wire is bent or cut.
10. When the lead of this product is soldered, pay attention as follows to avoid the decline of element characteristic or break down the element.
  - 10.1. Use Rosin type flux or non-activated flux(the content of chlorine shall be less than 0.2%)
  - 10.2. Do not dip the body into flux. (Flux shall be coated to lead wire only for soldering.)
  - 10.3. The pre-heat up should be conducted without melting the soldering of this product.
11. Do not apply tensile force or separating force to lead wire at soldering.
12. "Do not touch the resin case by soldering iron. The soldering point shall be min. 5 mm away from the root of lead wire. Please solder the following conditions.
  - Iron Tip Temperature : 360 degree C max.
  - Soldering Time : 4 seconds max. / 1 terminal
  - Number of Soldering : 1"
13. To keep solderability of product from declining, following storage condition is recommended.
  - 13.1. Storage condition Temperature : -10 to 40°C; Humidity : less than 75%RH (not dewing condition)
  - 13.2. Term : Please use this product within 6 months after shipment by first-in and first-out stocking system.
  - 13.3. Handling after unpacking of the minimum package: Reseal it promptly or store it seal open inside a sealed container with a drying agent
  - 13.4. Place: Do not store this product in corrosive gas(SO<sub>x</sub>, Cl etc) or under sun-light.
14. Discarded treatment :
  - 14.1. Recycling
  - 14.2. Recovery processing by a professional electronic component recycling company
  - 14.3. Send back to our department

## Revision

Version	Revised Content	Date	Approver
V0	Initial Issue	2026.2.4	ZQF

## Disclaimer

All products, datasheets and data can be changed without prior notice.

C&B Electronics Shenzhen CO., LTD., its affiliates, distributors, employees, and any other person acting on its behalf (collectively referred to as "C&B Electronics") shall not bear any legal responsibility for any errors, inaccuracies, or incompleteness of information related to the product disclosed under this agreement or other disclosures.

Product datasheet does not constitute an extension or revision of the purchase terms and conditions in C&B Electronics, including but not limited to the warranties under this agreement.

Unless specified in the purchase terms and conditions, C&B Electronics makes no guarantees, representations or warranties.

**To the maximum extent permitted by applicable laws, C&B Electronics hereby makes the following disclaimer:**

- (1) All liabilities arising from the use of the product;**
- (2) Including but not limited to all liabilities arising from special, indirect or incidental damages;**
- (3) All implied warranties, including warranties of suitability for special purposes, non infringement possibility, and marketability.**

The information provided in the datasheet and parameter tables may vary in different applications, and the performance of the product may change over time. The recommended application instructions for the product are based on C&B Electronics' understanding and experience of typical requirements. Customers are obligated to verify whether the product is suitable for a specific application based on the parameters provided in the datasheet. Before officially installing or using the product, you should ensure that you have obtained the latest version of relevant information, which can be obtained through the website: [resistor.today](http://resistor.today).

The signing of this agreement does not constitute an express, implied or other form of license related to all intellectual property rights of C&B Electronic Products.

Unless explicitly stated, the products listed in this agreement are not applicable to lifesaving or life sustaining products. In the absence of a clear indication, the customer shall bear all risks caused by unauthorized use of the above products and agree to fully compensate C&B Electronics for all losses caused by such sales or use. For written product terms for such special applications, please contact authorized personnel from C&B Electronics to obtain.

The names and markings on the listed products may be trademarks owned by others.