



Technical parameter

		LEVEL	
PROJECT		A[better product]	B[average product]
Electrical Properties	Contact Rating	0.1A, 12V DC MAX.	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC	Skey/PD: 100MΩ min.300V DC
	Withstand Voltage	100V AC for 1 minute	100 V AC for 1 minut
	Durable Performance	There No Load	35,000 Cycles
Rated Load		30,000 Cycles	25,000 Cycles
Storage temp.		-10℃～+65℃(Operating Temp:)	
Operating Force		0. 35N. (1N.=100gram-force) ±0. 1N	
Heat Rrsistance		IR Reflow:255℃, 5sec. Manual :350℃, 3sec.	

Unit:mm



Operation:DIP/立插式 大行程小型 检测开关 [操作力可定制]

ITEM NO.:TC-113 (Series)

(L6.0×W4.0×H8.8mm DETECTOR-SWITCH)

正向操作 DOWN

精密部品 NICETY

STABILIZE

適合環保 RoHS

No.	NAME	Description
① A	拨柄	POM 黑色塑料
② B	接触片	镀银&C5191R-H 磷铜
③ C	弹簧	SUS-304 不锈钢丝
④ D	上盖	POM 透明塑料
⑤ E	基座	PA66 黑色塑料
⑥ F	嵌件	镀银&C5191R-H 磷铜 t=0.15

CIRCUIT DIAGRAM

