



REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK



电路原理图



孔位尺寸

- Note:
- 1.Material:
- 1.1 Housing: High temperature thermoplastic,UL94v-0
 - 1.2 Orbit: High temperature thermoplastic,UL94v-0
 - 1.3 Contact: copper alloy;;
Gold plated contact area;Tin plated solder area
 - 1.4 Shell:Stainless;Ni plated allover;
Gold plated solder area
- 2.Specification:
- 2.1 Current rating: **0.5A** Max
 - 2.2 Voltage rating: **16V** DC
 - 2.3 Dielectric withstanding voltage:
500V(AC) for 1 min.
 - 2.4 Contact resistance: 100mΩ Max.
 - 2.5 Insulation resistance: 1000MΩ min.
 - 2.6 Temperature range: -25°C~85°C
 - 2.7 Mating cycle: **25000** cycles min
 - 2.8 Insert force:0.5 N Max
Extraction force: 0.5 N

⑦	内滑块	1	POM	黑色	
⑥	焊锡脚	3	黄铜 t=0.30mm	镀银	
⑤	基座	1	PPA	黑色	
④	盖子	1	尼龙	黑色	
③	弹簧	1	钢丝		
②	簧片	1	覆银铜	镀银	
①	按柄	1	POM	黑色	
序号	零件名称	数量	材质、规格	颜色\镀层	备注

DIMENSION CLASSIFICATION		台灣碩方精密電子科技有限公司		TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD		開關、連接器		SOFNG	
■ ; CRITICAL		TITLE		TC-306D 撬杆型检测开关		立插式中型大行程		SERIES SD106	
☒ ; MAJOR		TOLERANCE TABLE		PART NO.		TC-306D		DWG NO.	
				APPROVED		Peck		SCALE 1:1	
				CHECKED		Paul		UNIT mm	
				DRAWIN		David		REV AO	
				SIZE A4		SHEET NO.		1/1	

邀您使用(微信)小程序

碩方电子开关&连接器选型手册

手机扫码即可进入

