

Operation: SMT/卧式 小型 检测开关[操作力可定制]



LTEM NO.: TC-621 (Series)

(L3.0×W3.5×H1.4 DETECTOR-SWITCH)






Technical parameter


PROJECT	LEVEL	A[better product]	B[average product]
Electrical Properties	Contact Rating	50mA, 24V DC	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	200V AC for 1 minute	100 V AC for 1 minute
Durable Performance	There No Load	60,000 Cycles	50,000 Cycles
	Rated Load	50,000 Cycles	40,000 Cycles
	Storage temp.	-20℃~+75℃(Operating Temp:)	
	Operating Force	0.5N. (1N.=100gram-force)	
	Heat Rrsistance	IR Reflow:235℃, 5sec. Manual:350℃, 3sec.	

Unit:mm

CIRCUIT DIAGRAM



P.C.B LAYOUT



邀您使用(微信)小程序
碩方电子开关&连接器选型手册
手机扫码即可进入...