


Product Summary

- V_{DS} 60 V
- I_{DS} 80A
- $R_{DS(ON)}$ (at $V_{GS}=10$) $\leq 5.5m\Omega$ (Typ)
- Low Gate Charge Minimize Switching Loss

Application


- Adaptor
- Charger
- Power management
- SMPS Standby Power

Package and Pin Configuration



TO-252

Circuit diagram



Absolute Maximum Ratings

($T_A=25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	Value	UNIT
Drain-Source Voltage	V_{DS}	60	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current	I_D	80	A
Continuous Drain Current ($T_C=100^\circ\text{C}$)	I_D	42	A
Pulsed Drain Current (Note 1)	I_{DM}	270	A
Maximum Power Dissipation @ $T_A=25^\circ\text{C}$	P_D	100	W
Operating Junction Temperature Range	T_J	+150	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	-55 to +150	$^\circ\text{C}$
Thermal Resistance, Junction to Case	$R_{\theta JC}$	2.1	$^\circ\text{C/W}$

Note : When mounted on 1" square PCB (FR4 material).


Electrical Characteristics (T_A=25°C unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Static						
Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250μA	BV _{DSS}	60	--	--	V
Gate-Source Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	V _{GS(th)}	1.0	1.8	2.5	V
Gate-Source Leakage	V _{DS} =0V, V _{GS} = ±20V	I _{GSS}	--	--	±100	nA
Zero Gate Voltage Drain Current	V _{DS} = 60V, V _{GS} =0V	I _{DSS}	--	--	10	μA
Drain-Source On-State Resistance	V _{GS} = 10V, I _D = 40A	R _{DS(on)}	--	5.5	6.5	mΩ
	V _{GS} = 4.5V, I _D = 20A		--	7.1	9.5	mΩ
Forward Trans conductance	V _{DS} =10V, I _D =30A	g _{FS}	--	70	--	S
Dynamic (Note 2)						
Total Gate Charge (Note 3)	V _{DS} = 48V, I _D = 30A, V _{GS} = 4.5V	Q _g	--	33	--	nC
Gate-Source Charge (Note 3)		Q _{gs}	--	5.0	--	
Gate-Drain Charge (Note 3)		Q _{gd}	--	21	--	
Input Capacitance	V _{DS} = 25V, V _{GS} = 0V, F = 1.0MHz	C _{iss}	--	2660	--	pF
Output Capacitance		C _{oss}	--	280	--	
Reverse Transfer Capacitance		C _{rss}	--	200	--	
Switching						
Turn-On Delay Time (Note 3)	V _{DD} = 30V, I _D = 30A, V _{GS} = 10V, R _G = 3.3Ω	t _{d(on)}	--	10	--	nS
Rise Time (Note 3)		t _r	--	42	--	
Turn-Off Delay Time (Note 3)		t _{d(off)}	--	46	--	
Fall Time (Note 3)		t _f	--	80	--	
Source-Drain Diode Ratings and Characteristics (Note 2)						
Forward Voltage	V _{GS} = 0V, I _S = 10A	V _{SD}	--	0.8	1.2	V
Continuous Source Current	Integral reverse diode in the MOSFET	I _S	--	--	80	A
Pulsed Current (Note 1)		I _{SM}	--	--	270	A
Reverse recovery time	V _{GS} =0V, I _F =20A,	t _{rr}	--	25	--	nS
Reverse recovery charge	diF/dt=-100A/μs	Q _{rr}	--	24	--	nC


Notes:

1. Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 1%.
2. Guaranteed by design, not subject to production testing.
3. Independent of operating temperature


TYPICAL CHARACTERISTICS ($T_A=25^\circ\text{C}$ unless otherwise noted)




Typical Output Characteristics




Typical Output Characteristics




On-Resistance v.s. Gate Voltage



Normalized On-Resistance v.s. Junction Temperature




Forward Characteristic of Reverse Diode



Gate Threshold Voltage v.s. Junction Temperature

Package Outline Dimensions (unit: mm)

TO-252



Mounting Pad Layout (unit: mm)

