


# BNSP1003-01ETG

ESD Protection Diode

## Features

- 84Watts peak pulse power (tp = 8/20µs)
- Unidirectional configurations
- Solid-state silicon-avalanche technology
- Low clamping Voltage
- Low leakage current
- Protection one data/power line
- IEC 61000-4-2 ±30kV contact ; ±30kV air
- IEC 61000-4-4 (EFT) 40A (5/50ns)
- IEC 61000-4-5 (Lightning) 7A (8/20µs)

## Package




## Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation

## Mechanical Characteristics

- DFN1006 package
- Molding compound flammability rating: UL 94V-0
- Packaging: Tape and Reel
- RoHS/WEEE Compliant

## Marking




## Ordering information

| Order code     | Package | Base qty | Delivery mode |
|----------------|---------|----------|---------------|
| BNSP1003-01ETG | DFN1006 | 10k      | Tape and reel |



### Electrical Parameters ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

| Symbol    | Parameter                           |
|-----------|-------------------------------------|
| $I_{PP}$  | Maximum Reverse Peak Pulse Current  |
| $V_C$     | Clamping Voltage @ $I_{PP}$         |
| $V_{RWM}$ | Peak Reverse Working Voltage        |
| $I_R$     | Reverse Leakage Current @ $V_{RWM}$ |
| $V_{BR}$  | Breakdown Voltage @ $I_T$           |
| $I_T$     | Test Current                        |
|           |                                     |
|           |                                     |



Note: 8/20us pulse Waveform.

### Absolute Maximum Rating

| Rating                                         | Symler    | Value          | Units            |
|------------------------------------------------|-----------|----------------|------------------|
| Peak Pulse Power ( $t_p = 8/20\mu\text{s}$ )   | $P_{PP}$  | 84             | Watts            |
| Peak Pulse Current ( $t_p = 8/20\mu\text{s}$ ) | $I_{PP}$  | 7              | A                |
| ESD per IEC 61000-4-2 (Air)                    | $V_{ESD}$ | 30             | KV               |
| ESD per IEC 61000-4-2 (Contact)                |           | 30             |                  |
| Lead Soldering Temperature                     | $T_L$     | 260(10seconds) | $^\circ\text{C}$ |
| Junction Temperature                           | $T_J$     | -55 to + 150   | $^\circ\text{C}$ |
| Storage Temperature                            | $T_{stg}$ | -55 to + 150   | $^\circ\text{C}$ |

### Electrical Characteristics

| Parameter                 | Symler    | Conditions                                  | Min | Typical | Max | Units         |
|---------------------------|-----------|---------------------------------------------|-----|---------|-----|---------------|
| Reverse Stand-Off Voltage | $V_{RWM}$ | –                                           | –   | –       | 5.0 | V             |
| Reverse Breakdown Voltage | $V_{BR}$  | $I_T = 1\text{mA}$                          | 6.0 | 7.2     | 9.5 | V             |
| Reverse Leakage Current   | $I_R$     | $V_{RWM} = 5\text{V}, T = 25^\circ\text{C}$ | –   | 0.1     | 0.5 | $\mu\text{A}$ |
| Clamping Voltage          | $V_C$     | $I_{PP} = 7\text{A}, t_p = 8/20\mu\text{s}$ | –   | 10      | 12  | V             |
| Junction Capacitance      | $C_j$     | $V_R = 0\text{V}, f = 1\text{MHZ}$          | –   | 50      | 55  | pF            |





# BNSP1003-01ETG

ESD Protection Diode

## Typical Characteristics

Figure 1: Peak Pulse Power vs. Pulse Time




Figure 2: Power Derating Curve




Figure 3: Pulse Waveform






Figure 4: Clamping Voltage vs. I\_PP



# BNSP1003-01ETG


ESD Protection Diode

## Outline Drawing – DFN1006




| SYMBOL | MILLIMETER |      |      |
|--------|------------|------|------|
|        | MIN.       | Typ. | MAX. |
| A      | 0.55       | 0.60 | 0.65 |
| B      | 0.95       | 1.00 | 1.05 |
| C      | 0.45       | 0.50 | 0.55 |
| L      | 0.20       | 0.25 | 0.30 |
| F      | 0.05REF    |      |      |
| G      | 0.00       | 0.02 | 0.05 |
| H      | 0.45       | 0.50 | 0.55 |
| R      | 0.07       | 0.12 | 0.17 |

## Packaging Tape - DFN1006



| SYMBOL | MILLIMETER                             |
|--------|----------------------------------------|
| A0     | 0.71±0.05                              |
| B0     | 1.11±0.05                              |
| d0     | 1.5 <sup>+0.1</sup> <sub>-0</sub>      |
| d1     | 0.50±0.05                              |
| E      | 1.75±0.10                              |
| F      | 3.50±0.05                              |
| K0     | 0.56±0.05                              |
| P      | 2.00±0.05                              |
| P0     | 4.00±0.10                              |
| P1     | 2.00±0.05                              |
| W      | 8.00 <sup>+0.03</sup> <sub>-0.01</sub> |
| T      | 0.2±0.015                              |

## Packaging Reel



| SYMBOL   | MILLIMETER                      |
|----------|---------------------------------|
| A        | 178±1                           |
| B        | 3.5±0.2                         |
| C        | 14.3±0.2                        |
| D        | 9.8 <sup>+2</sup> <sub>-1</sub> |
| E        | 54.5±0.5                        |
| F        | 12.4±0.2                        |
| T1       | 1.0±0.2                         |
| Quantity | 10000PCS                        |

**BORN SEMICONDUCTOR, INC. ALL  
RIGHT RESERVED**

Specifications are subject to change without notice.

Please refer to <http://www.born-tw.com> for current information.

Revision: 2022-Jan-1-A

