

Reverse Voltage 6KV
Forward Current 5mA



绝对最大数值

Absolute Maximum Ratings

序号 No.	项目 Item	符号 Symbol	单位 Unit	数值 Rating	条件 Conditions
1	反向重复峰值电压 Repetitive Peak Reverse Voltage	V_{RRM}	KV	6	
2	反向不重复峰值电压 Non-Repetitive Peak Reverse Voltage	V_{RSM}	KV	8	
3	正向平均电流 Average Forward Current	$I_{F(AV)}$	mA	5	50HZ 正弦半波平均值, ($T_{amb}=50^{\circ}C$) 50HZ Sine-half Wave Rectification Average Value ($T_{amb}=50^{\circ}C$)
4	正向(不重复)浪涌电流 Non-Repetitive Forward Surge Current	I_{FSM}	A	0.5	50HZ 10ms 正弦半波 ($T_{amb}=25^{\circ}C$) 50HZ 10ms Sine-half Wave, ($T_{amb}=25^{\circ}C$)
5	工作环境温度 Ambient Temperature	T_{amb}	$^{\circ}C$	-40~+100	
6	最高结温 Maximum Junction Temperature	$T_{(vj)}$	$^{\circ}C$	120	
7	贮存温度 Storage Temperature	T_{stg}	$^{\circ}C$	-40~+120	

特征 Features

- 适用于高稳定显示器或电视接收机及办公类自动化设备
For high resolution displays or TV receivers and Working automation equipment
- 扩散结
Diffused-junction
- 具有良好的高温输出特性
Excellent high temperature output characteristics
(Small leakage current at high temperature and excellent reverse characteristics)

电特性(除非另有规定, $T_{amb}=25^{\circ}C$)

 Electrical Characteristics($T_{amb}=25^{\circ}C$, unless otherwise specified)

序号 NO.	项目 Item	符号 Symbol	单位 Unit	数值 Rating	测试条件 Test conditions
1	正向压降 Forward Voltage Drop	V_{FM}	V	20.0max	$I_{FM}=10mA$
2	常温反向漏电流 Normal Temperature Reverse Current	I_{RM1}	μA	2max	$V_{RM}=6KV$
3	高温反向漏电流 High Temperature Reverse Current	I_{RM2}	μA	5max	$T_{amb}=100^{\circ}C$ $V_{RM}=6KV$
4	结电容 Junction Capacitance	C_j	pF	1max	1MHZ, $V_B=0V$
5	反向恢复时间 Reverse Recovery Time	trr	μS	0.1 max	$I_F=2mA, I_{RM}=4 mA$ 脉冲前沿小于 $0.01 \mu S$ Fore edge of pulse less than $0.01 \mu s$

外形尺寸及标识

Dimensions and Marking

