






邀您使用(微信)小程序
硕方电子开关&连接器选型手册
手机扫码即可进入...

REVISION		
DESCRIPTION	DATE	APP
NEW RELEASE	03/03/2021	PECK



▨ =PATTERN PROHIBITED AREA
▨ =GND AREA
▨ =TIN AREA
TOLERANCE ±0.05



LEVEL		A[better product]	B[average product]
PROJECT	Contact Rating	0.3A, 30V DC	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	300V AC for 1 minute	250 V AC for 1 minut
Durable Performance	There No Load	15,000 Cycles	10,000 Cycles
	Rated Load	12,000 Cycles	8,500 Cycles
Storage temp.		-25℃~+75℃(Operating Temp:)	
Operating Force		2. 6N. (1N. =100gram-force) ±0. 5N	
Heat Rrsistance		IR Reflow:255℃,5sec. Manual:350℃,3sec.	

Material declaration		
No.	NAME	Description
1	拨柄	PA66 耐热尼龙塑料
2	盖板	PA66 耐热尼龙塑料
3	接线片	LCP 30%G/F (Black)耐热塑胶
4	按钮	PA66 耐热尼龙塑料
5	弹片	Beryllium bronze 镀青铜[单面镀银]
6	触点	Ag
7	按钮压柄	PA66 耐热尼龙塑料

DIMENSION CLASSIFICATION		台湾硕方精密电子科技有限公司		TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD		SOFNG	
■ : CRITICAL		TITLE		TC-313L 卧插式小型撬杆		開關,連接器	
☒ : MAJOR		TOLERANCE TABLE		微动开关		SD106	
.X		±	0.40	PART NO.	TC-313L	SERIES	
.XX		±	0.25	APPROVED	Peck	DWG NO.	TC-313
.XXX		±	0.10	CHECKED	Paul	SCALE 1:1	UNIT mm
ANGLE		±	2°	DRAWIN	David	REV	AO
						SHEET NO.	1/1