

<p>1</p> <p>保密等级: <input type="checkbox"/> 绝密 <input type="checkbox"/> 保密 <input type="checkbox"/> 普通</p> <p>符合RoHS 环保要求</p>	2	3	4	5	6	7	8																																				
A					<p>版次</p> <p>工程变更单号</p>	<p>基本描述</p>	<p>日期</p> <p>修订</p>																																				
B						<p>备注:</p> <p>1. 材质:</p> <p>1.1 胶芯: LCP+30%G.F UL94V-0</p> <p>1.2 端子: 高导电7025/C2680;</p> <p>1.3 外壳: SUS201/SUS304, T=0.30mm;</p> <p>1.4 中夹片: SUS301;</p> <p>2. 主要特性:</p> <p>2.1 额定电流: 3A/5A</p> <p>2.2 接触阻抗: 40mΩ MAX(初始值) 50mΩ MAX(测试后)</p> <p>2.3 绝缘阻抗: 100MΩ MIN</p> <p>2.4 耐压测试: 100V AC R.M.S.</p> <p>2.6 整体插入力: 5-20N 整体插入力: 5-20N (耐久后) 整体拔出力: 8-20N 整体拔出力: 6-20N (耐久后)</p> <p>2.7 耐久: 10000次</p> <p>2.8 耐高温: SMT回流焊 (峰值260° ±5°), 塑胶不能有起泡, 融胶等不良, 变色, 翘曲变形在公差范围以内;</p> <p>2.9 产品须做焊锡测试, 粘锡面积达到95%以上;</p> <p>3.0 盐雾测试: 24H MIN</p> <p>3.1 工作温度: -30℃~+85℃</p>																																					
C																																											
D						<table border="1"> <tr> <td>A1</td><td>GND</td><td>B12</td><td>GND</td></tr> <tr> <td>A4</td><td>VBUS</td><td>B9</td><td>VBUS</td></tr> <tr> <td>A5</td><td>CC1</td><td>B8</td><td>SBU2</td></tr> <tr> <td>A6</td><td>DP1</td><td>B7</td><td>DN2</td></tr> <tr> <td>A7</td><td>DN1</td><td>B6</td><td>DP2</td></tr> <tr> <td>A8</td><td>SBU1</td><td>B5</td><td>CC2</td></tr> <tr> <td>A9</td><td>VBUS</td><td>B4</td><td>VBUS</td></tr> <tr> <td>A12</td><td>GND</td><td>B1</td><td>GND</td></tr> <tr> <td>PIN</td><td>SIGNAL NAME</td><td>PIN</td><td>SIGNAL NAME</td></tr> </table>		A1	GND	B12	GND	A4	VBUS	B9	VBUS	A5	CC1	B8	SBU2	A6	DP1	B7	DN2	A7	DN1	B6	DP2	A8	SBU1	B5	CC2	A9	VBUS	B4	VBUS	A12	GND	B1	GND	PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND																																								
A4	VBUS	B9	VBUS																																								
A5	CC1	B8	SBU2																																								
A6	DP1	B7	DN2																																								
A7	DN1	B6	DP2																																								
A8	SBU1	B5	CC2																																								
A9	VBUS	B4	VBUS																																								
A12	GND	B1	GND																																								
PIN	SIGNAL NAME	PIN	SIGNAL NAME																																								
E	<p>RECOMMENDED P.C.B. LAYOUT TOLERANCE UNSPECIFIED ±0.05mm</p>																																										
F					<p>品名规格</p> <p>TYPE C16P板上四脚全贴板(三次模顶)</p>	<p>设计</p>																																					
G					<p>未注公差:</p> <p>.000 ±0.10</p> <p>.00 ±0.20</p> <p>.0 ±0.30</p> <p>角度 ±1°</p>	<p>产品料号</p> <p>TYPE16-N1S1-MT03-Z</p>	<p>审核</p>																																				
H					<p>图纸类型</p> <p>成品图</p>	<p>比例</p> <p>1:1</p>	<p>核准</p>																																				
1	2	3	4	5	6	7	8																																				