


4 mm Square Surface-Mount Miniature Trimmers Multi-Turn Cermet Sealed, Industrial Grade



FEATURES









- 0.25 W at 85 °C
- Wide ohmic range (10 Ω to 1 M Ω)
- Low contact resistance variation (2 % or 3 Ω)
- 4 mm design meets EIA SMD standard trimmer footprint
- Pick and place centering design, with flush adjustment
- Top and side adjust styles
- Construction: sealed (to withstand board wash processing)
- Industrial grade
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

LINKS TO ADDITIONAL RESOURCES



The TSM41 trimming potentiometer has been designed for surface mount applications and offers volumetric efficiency with high performance and stability.

DIMENSIONS in millimeters (± 0.5 mm)			
TSM41 ZL (SIDE ADJUST)	TSM41 ZJ (SIDE ADJUST)	TSM41 YL (TOP ADJUST)	TSM41 YJ (TOP ADJUST)
			
RECOMMENDED SOLDERING AREAS			
			

**ELECTRICAL SPECIFICATIONS**

Resistive element	Cermet
Electrical travel adjustment angle	11 turns $\pm$ 2 turns
Resistance range	10 Ω to 1 M Ω
Tolerance standard	$\pm$ 10 %
Power rating (300 V max.)	Linear 0.25 W at 85 °C 0 W at 150 °C
Circuit diagram	
Temperature coefficient	$\pm$ 100 ppm/°C
Contact resistance variation (typical)	2 % or 3 Ω
End resistance (typical)	1 Ω
Dielectric strength (RMS)	600 V (1 minute)
Insulation resistance (500 V _{DC})	100 M Ω

MECHANICAL SPECIFICATIONS

Torque	1.8 cm/V max.
End stop	Clutch action (2 turns max.)
Unit weight	Approximately 0.28 g
Wiper	Positioned at approx. 50 % (actual TR)

ENVIRONMENTAL SPECIFICATIONS

Temperature range	-55 °C to +140 °C
Sealing	Sealed container IP67
MSL level	1

SOLDERING RECOMMENDATIONS

Recommended reflow profile 2, see Application Note www.vishay.com/doc?52029

PERFORMANCES

TESTS	CONDITIONS	TYPICAL VALUES AND DRIFTS
Load life	1000 h at rated power 90°/30' - ambient temp. +85 °C	Total resistance shift = $\pm$ 3 Ω or $\pm$ 3 % whichever is greater
Humidity	MIL-STD-202 method 106	Total resistance shift = $\pm$ 2 % Insulation resistance = 10 M Ω
Thermal shock	5 cycles	Total resistance shift = $\pm$ 2 % Voltage resistance shift = $\pm$ 1 %
Rotational cycling	200 cycles	Total resistance shift = $\pm$ 3 Ω or $\pm$ 3 % whichever is greater
Shock	100 g	Total resistance shift = $\pm$ 1 % Voltage resistance shift = $\pm$ 1 %
Vibration	20 g	Total resistance shift = $\pm$ 1 % Voltage resistance shift = $\pm$ 1 %

Note

- Nothing stated herein shall be construed as a guarantee of quality or durability

STANDARD RESISTANCE ELEMENT DATA




STANDARD RESISTANCE VALUES	LINEAR LAW			TYPICAL TCR -55 °C +125 °C
	MAX. POWER AT 85 °C	MAX. WORKING VOLTAGE	MAX. CURRENT THROUGH ELEMENT	
Ω	W	V	mA	ppm/°C
10	0.25	1.58	158	± 100
20	0.25	2.23	112	
50	0.25	3.53	77	
100	0.25	5.00	50	
200	0.25	7.07	35	
500	0.25	11.2	22	
1K	0.25	15.8	15.8	
2K	0.25	22.3	11.2	
5K	0.25	35.3	7.1	
10K	0.25	50.0	5.0	
20K	0.25	70.7	3.5	
50K	0.25	112	2.2	
100K	0.25	158	1.6	
200K	0.25	223	1.12	
500K	0.08	300	0.83	
1M	0.04	300	0.83	



MARKING

Vishay trademark, ohmic value, manufacturing date

PACKAGING in millimeters

On tape and reel, by 500 pieces for Z version, 250 pieces for YJ version: code TR250, or 200 pieces for YL version.

TSM41 ZL

TSM41 ZJ

TSM41 YJ


PACKAGING in millimeters

ORDERING INFORMATION (part number)

T	S	M	4	1	Y	L	5	0	4	K	R	0	5				
MODEL		STYLE		OHMIC VALUE		TOLERANCE		PACKAGING		SPECIAL NUMBER							
TSM41		YJ YL ZJ ZL		From 10 Ω to 1 M Ω 504 = 500 k Ω		K = 10 %		R10 = reel 500 pieces for ZJ and ZL R05 = reel 250 pieces for YJ and 200 pieces for YL On request		(If applicable) Given by Vishay for custom design							

DESCRIPTION (for information only)

TSM41	YL	500K	10 %		TR	e3
MODEL	STYLE	VALUE	TOLERANCE	SPECIAL	PACKAGING	LEAD (Pb)-FREE

RELATED DOCUMENTS
APPLICATION NOTES

Potentiometers and Trimmers	www.vishay.com/doc?51001
Guidelines for Vishay Sfernice Resistive and Inductive Components	www.vishay.com/doc?52029



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.