








修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DWG		2016-03-12

1.MATERIAL
HOUSING:LCP UL 94V-0
ACTUATOR:LCP UL 94V-0
CONTACTS:COPPER ALLOY
PEG:COPPER ALLOY
2.PLATING:
CONTACTS:TIN OVER NICKEL
PEG:TIN OVER NICKEL
3.PART NO:
OPERATING VOLTAGE:50V AC,DC
CURRENT RATING:0.3A AC,DC
OPERATING TEMPERATURE:-25C~+85C



No. of Contacts	DIM.		
	A	B	C
12	14.70	8.80	10.45
24	24.30	18.40	20.05
28	27.50	21.60	23.25
30	29.10	23.20	24.85
32	30.70	24.80	26.45
34	32.30	26.40	28.05
36	33.90	28.00	29.65








APPLICABLE FPC




深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 	TITLE: 产品名称:0.8间距2.0高带扣掀盖式					
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: 0.8K-QX-nPWB			
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001

修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DIM		2016-03-12



No.of Contacts	DIM			REEL (CARTON)	SUM(PCS)
	A	B	C		
THD0820 4pin-12pin	24	11.5	—	10	20000
THD0820 28pin~32pin	44	20.2	40.4	6	12000
THD0820 33pin~36pin	56	26.25	52.5	5	10000



- NOTES:
- Component load per 13" reel: 2000 pcs
 - Material: black conductive polystyrene alloy.
 - Thickness: 0.3 ± 0.05 mm
 - All dimensions meet eia-481-c requirements

深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 	TITLE: 产品名称: 0.8间距2.0高带扣掀盖式				
X.X	± 0.30	X.X*	$\pm 3^\circ$	APPD: 核准:			
X.XX	± 0.20	X.XX*	$\pm 2^\circ$	CHECK: 校对: 王建业			
X.XXX	± 0.10	X.XXX*	$\pm 1^\circ$	DRAW: 绘图: 黄艳兰			
				PART NO: 产品编号: 0.8K-QX-nPWB			
				DATE	SCALE	UNIT	CODE NUMBER
				2016-03-12	1:1	mm	A001