











		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	



GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. .X ±0.30 .XX ±0.20 .XXX ±0.10 GENERAL ANGLE: X.° ±10° X.X° ±8° X.XX° ±5°		TITLE: USB CF 24P SMT TYPE TOP-MOUNT CH=1.6mm						
		DWG. NO.: UC20-0B24332P20			CHECKED: MAX			
		PART NO.: UC20-0B24332P20			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn		

1

3

4

5

