




**SPECIFICATIONS**

Current Rating:3Amps  
 Insulation Resistance:1000MΩ Min  
 Contact Resistance:20mΩ Max  
 Withstanding Voltage:AC 1000V  
 Operation Temperature:-40° to+105°  
 Contact Material:Brass  
 Insrlator Material:Polyester (UL 94V-0)  
 Contact plating:Gold Flash  
 Standard:PA6T  
 Max. Processing Temp: 240° C for30-60seconds  
 (260° Cfor10seconds)

P/N	PIN	DIM. A	DIM. B
HMT-2.54-2*3P-WJN	2*3	5.08	7.62
HMT-2.54-2*4P-WJN	2*4	7.62	10.16
HMT-2.54-2*5P-WJN	2*5	10.16	12.70
HMT-2.54-2*6P-WJN	2*6	12.70	15.24
HMT-2.54-2*7P-WJN	2*7	15.24	17.78
HMT-2.54-2*8P-WJN	2*8	17.78	20.32
HMT-2.54-2*9P-WJN	2*9	20.32	22.86
HMT-2.54-2*10P-WJN	2*10	22.86	25.40
HMT-2.54-2*12P-WJN	2*12	27.94	30.48
HMT-2.54-2*13P-WJN	2*13	30.48	33.02
HMT-2.54-2*14P-WJN	2*14	33.02	35.56
HMT-2.54-2*15P-WJN	2*15	35.56	38.10
HMT-2.54-2*16P-WJN	2*16	38.10	40.64
HMT-2.54-2*17P-WJN	2*17	40.64	43.18
HMT-2.54-2*18P-WJN	2*18	43.18	45.72
HMT-2.54-2*20P-WJN	2*20	48.26	50.80
HMT-2.54-2*22P-WJN	2*22	53.34	55.88
HMT-2.54-2*25P-WJN	2*25	60.96	63.50
HMT-2.54-2*30P-WJN	2*30	73.66	76.20
HMT-2.54-2*32P-WJN	2*32	78.74	81.28



GENERAL TOLERANCES UNLESS SPECIFIED		 <b>深圳市华明通电子有限公司</b> Shenzhen Huamingtong Electronics Co., Ltd			
X.±0.30	X.°±5°	PART NO.	TITLE: 2.0DC3-nPin H5.7 90度		
.X±0.20	.X°±1°	HMT-2.54-2*NP-WJN	PC2.8 PB9.3 L10.5/14.5 6T		
.XX±0.10	.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	
MANUFACTURE DWG		CHED: Talen		A4	UNITS
		APPD: Sophia		SCALE	SHEET
				N:A	1/1