


**SPECIFICATIONS**

Current Rating: 3Amps  
 Insulation Resistance: 1000M  $\Omega$  Min  
 Contact Resistance: 20m  $\Omega$  Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature:  $-40^{\circ}$  to  $+105^{\circ}$   
 Contact Material: Brass  
 Insulator Material: Polyester (UL 94V-0)  
 Contact plating: Gold Flash  
 Standard: PA6T  
 Max. Processing Temp:  $240^{\circ}$  C for 30-60seconds  
 ( $260^{\circ}$  C for 10seconds)

P/N	PIN	DIM. A	DIM. B
HMT-2.54-2*3P-JN	2*3	5.08	7.62
HMT-2.54-2*4P-JN	2*4	7.62	10.16
HMT-2.54-2*5P-JN	2*5	10.16	12.70
HMT-2.54-2*6P-JN	2*6	12.70	15.24
HMT-2.54-2*7P-JN	2*7	15.24	17.78
HMT-2.54-2*8P-JN	2*8	17.78	20.32
HMT-2.54-2*9P-JN	2*9	20.32	22.86
HMT-2.54-2*10P-JN	2*10	22.86	25.40
HMT-2.54-2*12P-JN	2*12	27.94	30.48
HMT-2.54-2*13P-JN	2*13	30.48	33.02
HMT-2.54-2*14P-JN	2*14	33.02	35.56
HMT-2.54-2*15P-JN	2*15	35.56	38.10
HMT-2.54-2*16P-JN	2*16	38.10	40.64
HMT-2.54-2*17P-JN	2*17	40.64	43.18
HMT-2.54-2*18P-JN	2*18	43.18	45.72
HMT-2.54-2*20P-JN	2*20	48.26	50.80
HMT-2.54-2*22P-JN	2*22	53.34	55.88
HMT-2.54-2*25P-JN	2*25	60.96	63.50
HMT-2.54-2*30P-JN	2*30	73.66	76.20
HMT-2.54-2*32P-JN	2*32	78.74	81.28

GENERAL TOLERANCES UNLESS SPECIFIED		 <b>深圳市华明通电子有限公司</b> Shenzhen Huamingtong Electronics Co., Ltd	
X. $\pm 0.30$	X. $^{\circ} \pm 5^{\circ}$	PART NO. HMT-2.54-2*NP-JN	TITLE: 2.54DC3-NP in H8.9 180度 PC3.2 L11.5 6T
.X $\pm 0.25$	.X $^{\circ} \pm 1^{\circ}$	DESIGN: James	CUSTOMER
.XX $\pm 0.20$	.XX $^{\circ} \pm 0.5^{\circ}$	CHED: Talen	
MANUFACTURE DWG		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1