



SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000MΩ, Min
 Contact Resistance: 20mΩ, Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30-60seconds
 (260° C for 5seconds)

P/N	PIN	DIM. A	DIM. B
HMT-2.0-2*3P-ZJN	2*3	4.00	6.00
HMT-2.0-2*4P-ZJN	2*4	6.00	8.00
HMT-2.0-2*5P-ZJN	2*5	8.00	10.00
HMT-2.0-2*6P-ZJN	2*6	10.00	12.00
HMT-2.0-2*7P-ZJN	2*7	12.00	14.00
HMT-2.0-2*8P-ZJN	2*8	14.00	16.00
HMT-2.0-2*9P-ZJN	2*9	16.00	18.00
HMT-2.0-2*10P-ZJN	2*10	18.00	20.00
HMT-2.0-2*11P-ZJN	2*11	20.00	22.00
.....
HMT-2.0-2*35P-ZJN	2*35	PIN-2.00	PIN

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.±0.30	X.°±5°	PART NO. HMT-2.0-2*NP-ZJN	TITLE: 2.0DC3-nPin H5.7 180度 PC2.8 L8.0 6T
.X±0.20	.X°±1°	DESIGN: James	CUSTOMER
.XX±0.10	.XX°±0.5°	CHED: Talen	
MANUFACTURE DWG		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1