






1
RoHS Compliant

7
浙江博穆精密电子有限公司
BOOM PRECISION ELECTRONICS CO.,LTD.ZHEJIANG



NOTE:
Poles: 2~16
Voltage rating: 250V DC/AC
Current rating: 3.0A
Withstand voltage: 1000V AC
Working Temperature: -40° C~+105° C
Insulation Resistance: 1000MΩ (MIN)
Contact Resistance: 10mΩ (MAX)
Material: PA66 UL 94V-0
Contact: □ 0.64mm Brass
Coating: Ni≥20 μ" + Tin≥80 μ"



2510-nA
系列名称
PIN数

Circuits	Dim.A	Dim.B	Circuits	Dim.A	Dim.B
2	2.54	5.08	12	27.94	30.48
3	5.08	7.62	13	30.48	33.02
4	7.62	10.16	14	33.02	35.56
5	10.16	12.70	15	35.56	38.10
6	12.70	15.24	16	38.10	40.64
7	15.24	17.78	17	40.64	43.18
8	17.78	20.32	18	43.18	45.72
9	20.32	22.86	19	45.72	48.26
10	22.86	25.40	20	48.26	50.80
11	25.40	27.94			

PCB LAYOUT



PART NO.	2510-NA			修改内容	修改日期	修改人	修改版本	APPROVAL
				图纸新发	2022. 10. 31	MK	A	DRAWN: MK
TITLE	2.54mm Wire to Board							CHECKED:
THIRD ANGLE	SCALE	UNIT	SHEET NO	TOLERANCE	DATE	PAGE NO	REV	APPROVED:
	1:1	mm	A4	.X±0.20 .XXX±0.05 .XX±0.10 ANGLE±2°	2022. 10. 31	1/1	A	QH