

FEATURES


- For surface mounted applications
- Glass Passivated Chip Junction
- Fast reverse recovery time
- Ideal for automated placement
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SOD-323
- Terminals: Solderable per MIL-STD-750, Method 2026

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Top View
Simplified outline SOD-323 and symbol



Absolute Maximum Ratings at 25 °C

Parameter	Symbols	BAV21WS	Units
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	250	V
Maximum RMS voltage	V_{RMS}	200	V
Continuous Forward Current	I_F	250	mA
Repetitive Peak Forward Current	I_{FRM}	625	mA
Non-reptitive Peak Forward Surge Current	I_{FSM}	1 3 9	A
		at 1s	
		at 1ms	
		at 1 us	
Total Power Dissipation	P_{tot}	500	mW
Operating and Storage Temperature Range	T_j, T_{stg}	-55 ~ +150	°C

Characteristics at $T_a = 25\text{ }^\circ\text{C}$

Parameter	Symbols	BAV21WS	Units
Reverse Breakdown Voltage at $I_R=100\mu\text{A}$	$V_{(BR)R}$	250	V
Maximum Forward Voltage at 100 mA at 200 mA	V_F	1.00 1.25	V
Maximum DC Reverse Current at Rated DC Blocking Voltage $T_a = 25\text{ }^\circ\text{C}$ $T_a = 150\text{ }^\circ\text{C}$	I_R	0.1 100	μA
Typical Junction Capacitance at $V_R=4\text{V}$, $f=1\text{MHz}$	C_j	5	pF
Maximum Reverse Recovery Time	t_{rr}	50	ns

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Instantaneous Forward Characteristics






Fig.4 Typical Junction Capacitance



Package information (Unit: mm)

SOD-323



Mounting Pad Layout (Unit: mm)

