


NO.	ECN NO.	DESCRIPTION	DATE
1			

客户图



Note:

- Material(材料):**
 Barrel: Brass C3604 (针管: 黄铜 C3604)
 Plunger: Brass C3604 (针头: 黄铜 C3604)
 Spring: SUS304 (弹簧: SUS304)
- Plating(电镀):**
 Barrel: 3u' Au over 50~80u Ni (针管: 镀金3u', 镍底50~80u')
 Plunger: 3u' Au over 50~80u Ni (针头: 镀金3u', 镍底50~80u')
 Spring: No plated (弹簧: 不电镀)
- Electrical(电气特性):**
 Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)
 Contact Resistance: 100 mohm Max. at working height.
 接触电阻: 最大100毫欧 (在工作高度状态下)
- Mechanical(机械性能):**
 Force: 70g±20% at working height. (70g±20% 在工作高度)。
 Durability: 10,000 cycles(min) (寿命: 10000次)
- WorkTemperature(工作环境):**
 Withstanding Higt Temperature: 280℃
 Operational Temperature: ?40℃~ ?85℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM
 TEL.: 0755-28773277 FAX: 0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2016.04.13	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH	ANGLE
X.XX ±0.05mm	X.XX ±0.50°
X.X ±0.10mm	X.X ±1.00°
X. ±0.20mm	X. ±2.00°

DESIGNED BY:	DWG. NO. YZ130115073P-02
CHECKED BY:	TITLE: Pogo pin连接器
APPROVED BY:	