



# 客户图



**Note:**

- 1: Material(材料) :  
 Barrel: Brass C3604 (针管: 黄铜 C3604)  
 Plunger: Brass C3604 (针头: 黄铜 C3604)  
 Spring: SUS304 (弹簧: SUS304)  
 Plating(电镀) :  
 Barrel: 5u' Au over 50~80u' Ni(针管: 镀金5u', 镍底50~80u'.)  
 Plunger: 5u' Au over 50~80u' Ni (针头: 镀金5u', 镍底50~80u'.)  
 Spring: Gold flash (弹簧: 镀金)
- 2: Electrical(电气特性) :  
 Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)  
 Contact Resistance: 50 mohm Max. at working height.  
 接触电阻: 最大50毫欧 (在工作高度状态下)
- 3: Mechanical(机械性能) :  
 Force: 120g±20% at working height. (120g±20% 在工作高度)。  
 Durability: 10,000 cycles(min) (寿命: 10000次)
- 4: WorkTemperature(工作环境):  
 Withstanding Higt Temperature: 280℃  
 Operational Temperature: -20℃~ +70℃

NO.	ECN NO.	DESCRIPTION	DATE
-----	---------	-------------	------

<b>深圳市鑫探技术有限公司</b> HTTP://WWW.XYZPOGOPIN.COM TEL: 0755-28773277 FAX: 0755-28891353			
SCALE:	N/A	UNIT:	mm
SHEET:	1 of 1	PROJECTION:	⊕
DATE:	2026.04.11	VER.	A.0
THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
XXX	±0.05mm	XXX	±0.50°
XX	±0.10mm	XX	±1.00°
X	±0.20mm	X	±2.00°
DESIGNED BY:	CHECKED BY:	DWG. NO.	YZ01715085R-03
APPROVED BY:		TITLE:	Pogo pin