





SPECIFICATIONS

Current Rating:0.75 Amps
 Withstanding Voltage:AC 500V
 Insulation Resistance:1000MΩ Min
 Contact Resistance:20mΩ Max
 Operation Temperature:-40°to+105°
 Insulator Material:Polyester(UL94V-0)
 Contact Material:Phosphor bronze
 Standard:PA6T
 Contact Plating:Gold Flash
 Max.Processing Temp:240°C for30-60seconds
 (260°C for5seconds)



P/N	PIN	DIM.A	DIM.B
BX-PM1.0-2-01PU-W	2*1	0.00	1.00
BX-PM1.0-2-02PU-W	2*2	1.00	2.00
BX-PM1.0-2-03PU-W	2*3	2.00	3.00
BX-PM1.0-2-04PU-W	2*4	3.00	4.00
BX-PM1.0-2-05PU-W	2*5	4.00	5.00
BX-PM1.0-2-06PU-W	2*6	5.00	6.00
BX-PM1.0-2-07PU-W	2*7	6.00	7.00
BX-PM1.0-2-08PU-W	2*8	7.00	8.00
BX-PM1.0-2-09PU-W	2*9	8.00	9.00
.....
BX-PM1.0-2-40PU-W	2*40	(PIN-1)	(PIN)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-PM1.0-2-NPU-W		版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA		品名 TITLE	1.0FH H2.0 2xNPin SMT W2.5 U# PC3.8 PB2.3 6T		页次 SHEET	1/1
			.X±0.20	.X*±1°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.10	.XX*±0.5°	单位 UNITS	MM	比例 SCALE	1:1				