





REV.	DESCRIPTION	ECN NO.	NAME	DATE

1  
2  
3  
4  
5



- , MATERIAL:
1. Insulator: PBT+30% Glass Fiber
  2. Contact: Brass
  3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
  4. Shell: Steel, Nickel Plated
- , SPECIFICATION:
1. Current Rating: 3 AMPS
  2. Insulation Resistance: 100MΩ MIN. At 500VDC
  3. Dielectric Strength: 500V for One minute
  4. Operation Temperature: -55° C ~ +105° C.

✳️【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)  
PCB TOLERANCE: ±0.05

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM. TOL.	TITLE: DR9M叉锁			CHECKED: MAX	
x. ±0.30	DWG. NO.: D-SUB-18-0816-9PWZ				
x.x ±0.25	PART NO.: D-SUB-18-0816-9PWZ			DRAWN: ELLA	
x.xx ±0.15	UNIT: mm			APPROVED: WILL	
GENERAL ANGLE:	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	
x. ±5.0°					
x.x' ±2.0°					
x.xx' ±1.0°					