

**FEATURE**

**Maximum output current**



$I_{OM}: 0.1\text{ A}$

**Output voltage**

$V_O: 15\text{ V}$

**Continuous total dissipation**

$P_D: 0.5\text{ W}$




**ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)**

Parameter	Symbol	Value	Units
Input Voltage	$V_I$	30	V
Operating Junction Temperature Range	$T_{OPR}$	0~+150	°C
Storage Temperature Range	$T_{STG}$	-55~+150	°C

**ELECTRICAL CHARACTERISTICS AT SPECIFIED VIRTUAL JUNCTION TEMPERATURE**








Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Output voltage	$V_O$	$25^\circ\text{C}$	14.4	15	15.6	V
		$17.5\text{V} \leq V_I \leq 30\text{V}, I_O = 1\text{mA} - 40\text{mA}$	14.25	15	15.75	V
		$0 - 125^\circ\text{C}$ $V_I = 23\text{V}, I_O = 1\text{mA} - 70\text{mA}$	14.25	15	15.75	V
Load Regulation	$\Delta V_O$	$I_O = 1\text{mA} - 100\text{mA}, V_I = 23\text{V}$ $25^\circ\text{C}$		25	150	mV
		$I_O = 1\text{mA} - 40\text{mA}, V_I = 23\text{V}$ $25^\circ\text{C}$		15	75	mV
Line regulation	$\Delta V_O$	$17.5\text{V} \leq V_I \leq 30\text{V}, I_O = 40\text{mA}$ $25^\circ\text{C}$		65	300	mV
		$19\text{V} \leq V_I \leq 30\text{V}, I_O = 40\text{mA}$ $25^\circ\text{C}$		58	250	mV
Quiescent Current	$I_q$	$25^\circ\text{C}$		4.6	6.5	mA
Quiescent Current Change	$\Delta I_q$	$19\text{V} \leq V_I \leq 30\text{V}, I_O = 40\text{mA}$ $0 - 125^\circ\text{C}$			1.5	mA
	$\Delta I_q$	$1\text{mA} \leq I_O \leq 40\text{mA}, V_I = 23\text{V}$ $0 - 125^\circ\text{C}$			0.1	mA
Output Noise Voltage	$V_N$	$10\text{Hz} \leq f \leq 100\text{KHz}$ $25^\circ\text{C}$		82		$\mu\text{V}$
Ripple Rejection	RR	$18.5\text{V} \leq V_I \leq 28.5\text{V}, f = 120\text{Hz}$ $0 - 125^\circ\text{C}$	34	39		dB
Dropout Voltage	$V_d$	$25^\circ\text{C}$		1.7		V

**TYPICAL APPLICATION**




Note: Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.

RATING AND CHARACTERISTIC CURVES




Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ( $T_{s(min)}$ )	+150 °C
	-Temperature Max ( $T_{s(max)}$ )	+200 °C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp ( $T_L$ ) to peak)		3 °C/sec. Max
$T_{s(max)}$ to $T_L$ - Ramp-up Rate		3 °C/sec. Max
Reflow	-Temperature ( $T_L$ ) (Liquid us)	+217 °C
	-Temperature ( $t_L$ )	60-150 secs.
Peak Temp ( $T_P$ )		+260(+0/-5) °C
Time within 5 °C of actual Peak Temp ( $t_p$ )		30 secs. Max
Ramp-down Rate		6 °C/sec. Max
Time 25 °C to Peak Temp ( $T_P$ )		8 min. Max
Do not exceed		+260 °C




Package Dimensions & Suggested Pad Layout


SOT89



Top View



Side View




Symbol	A	b	b1	C	D	D1	E	E1	e	e1	H	L	
Dimensions (mm)	MIN	1.40	0.44	0.36	0.3	4.40	1.50	2.29	2.00 <sup>f</sup>	1.50 BSC	3.00 BSC	3.94	0.89
	NOM	-	-	-	-	-	-	-	-	-	-	-	-
	MAX	1.60	0.56	0.48	0.5	4.60	1.75	2.60	2.29	-	-	4.25	1.20

Dimensions	Value (in mm)
C	2.50
G	3.60
X	1.40
X1	0.90
X2	0.90
Y	1.40
Y1	2.60
Y2	1.50
Y3	0.90

Tape & reel specification

Tape



Symbol	Dimension (mm)
--------	----------------

P0	4.00±0.20
----	-----------

P1	8.00±0.20
----	-----------

P2	2.00±0.20
----	-----------

D0	1.60±0.20
----	-----------

D1	1.60±0.20
----	-----------

E	1.75±0.20
---	-----------

F	7.50±0.15
---	-----------

W	16.00±0.20
---	------------


A0	6.30±0.20
----	-----------

B0	8.25±0.20
----	-----------

K0	2.60±0.20
----	-----------

T	0.23±0.10
---	-----------

13" Reel



D2	180.0±5.0
----	-----------

D3	60Min.
----	--------

D4	R32.0±2.0
----	-----------

G	R86.5±2.0
---	-----------

H	R30.0±2.0
---	-----------

I	13.0±2.0
---	----------

W1	13.20±2.0
----	-----------

W2	16.50±2.0
----	-----------

Quantity: 1000PCS