




REV.	Q'TY	ECN. NO.	APR.	DATE





技术要求 Specification:

1. 材质 Material: PA66 UL94V-0:
2. 额定电流 Current rating: 2.0A AC, DC
3. 额定电压 Voltage rating: 100V AC, DC
4. 温度范围 Temperature range: -25℃ to +85℃
5. 接触电阻 Contact resistance: ≤ 20mΩ
6. 绝缘电阻 Insulation resistance: > 1000MΩ
7. 耐压 Withstand voltage: 800V AC/minute
8. 塑件表面平整光滑, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



Part No	Pin	A	B	C
XY-PHR-2PJK	2	2.00	5.70	4.50
XY-PHR-3PJK	3	4.00	7.70	6.50
XY-PHR-4PJK	4	6.00	9.70	8.50
XY-PHR-5PJK	5	8.00	11.70	10.50
XY-PHR-6PJK	6	10.00	13.70	12.50
XY-PHR-7PJK	7	12.00	15.70	14.50
XY-PHR-8PJK	8	14.00	17.70	16.50
XY-PHR-9PJK	9	16.00	19.70	18.50
XY-PHR-10PJK	10	18.00	21.70	20.50
XY-PHR-11PJK	11	20.00	23.70	22.50
XY-PHR-12PJK	12	22.00	25.70	24.50
XY-PHR-13PJK	13	24.00	27.70	26.50
XY-PHR-14PJK	14	26.00	29.70	28.50
XY-PHR-15PJK	15	28.00	31.70	30.50
XY-PHR-16PJK	16	30.00	33.70	32.50



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co., Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR. Alex	TITLE: PH2.0MM HOUSING		
.X±0.3	.X*±5°	CHK. Jack	DWG NO. XY-PHR-NPJK		
.XX±0.2	.X*±3°	DRA. Can	PROJ.	CUSTOMER DRAWING	
.XXX±0.1	.XX*±1°	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A