

MBR30L300CD

Mos-Controlled Schottky Barrier Rectifiers



Voltage: 300 Volts

Current: 30 Amperes

Polarity And Marking

Package: TO-263

Features

- NH'S MOS Technology Schottky Barrier Chip Technology
- Super Low Forward Voltage Drop For High Efficiency
- Low Power Loss For High Reliability
- High Frequency Switching Speed

Mechanical Data

- **Case:** Molded With UL-94 ClassV-0 Recognized, RoHS-Compliant
- **Polarity:** Look At The Polarity And Marking On The Right
- **Terminals:** Tin Plated Leads,Solderable Per J-STD-002 And JESD22-B102
- **Weight:**App. 2.057 Grams (0.072557 Ounce)

Typical Applications

- Switch Mode Power Supplies (SMPS)
- Fast Chargers
- LED Driver And Monitor Lighting
- Automotive Electronics And Charging Posts

Remark:

- ①. NH=Niuhan Trademark
- ②. FF=Product Line Code,According To Actual Changes
YWW=Date Code,According To Actual Changes
LLWWF=Internal Code,According To Actual Changes
- ③. MBR30L300CD=Model

Single Phase,Half Wave,60Hz,Resistive Or Inductive Load.For Capacitive Load,Derate Current By 20%

Maximum Ratings (Ta=25°C Unless Otherwise Specified)

Parameter	Test Conditions	Symbol	Ratings	Unit
Maximum Repetitive Peak Reverse Voltage		V_{RRM}	300	V
Maximum RMS Voltag		V_{RMS}	210	V
Maximum DC Blocking Voltage		V_{DC}	300	V
Maximum Average Forward Rectified Current		$I_{F(AV)}$	30	A
Peak Forward Surge Current Per Diode	8.3ms Single Half Sine-wave Superimposed On Rate Load	I_{FSM}	200	A
Current Squared Time Per Diode	$t < 8.3$ ms	$I^2 t$	166.0	A ² sec

Electrical Characteristics (Ta=25°C Unless Otherwise Specified)

Parameter	Test Conditions	Symbol	Ratings			Unit
			Min.	Typ.	Max.	
Instaneous Forward Voltage Per Diode	Ta=25°C Ta=125°C $I_F = 15.0$ A	V_F	-- --	0.93 0.89	1 0.96	V
Maximum DC Reverse Current at Rated DC Blocking Voltage	Ta=25°C Ta=125°C $V_R = V_{RRM}$	I_{RRM}	-- --	1 0.5	5 5	uA mA
Typical Junction Capacitance Per Diode	4 V,1MHz	C_J	--	130.0	--	pF

Thermal Characteristics (Ta=25°C Unless Otherwise Specified)

Parameter	Test Conditions	Symbol	Typ.	Unit
Operating Junction Temperature Range		T_J	-55 to 150	°C
Storage Temperature Range		T_{STD}	-55 to 150	
Thermal Resistance Junction To Ambient With Steady-State	Still Air Environment With Ta=25°C	$R_{\theta JA}$	62.5	°C/W
Thermal Resistance Junction-Case With Steady-State	Device Mounted On 1 in2 FR-4 Board With 2oz. Copper	$R_{\theta JC}$	2.0	

Notes: 1.Pulse Test: 300 Us Pulse Width,1% Duty Cycle

MBR30L300CD

Mos-Controlled Schottky Barrier Rectifiers



Typical Characteristics Curves




Fig.1-FORWARD CURRENT DERATING CURVE




Fig.2- TYPICAL INSTANTANEOUS FORWARD




Fig.3- TYPICAL REVERSE CHARACTERISTICS




Fig.4- TYPICAL JUNCTION CAPACITANCE




Fig.5-MAX. NON-REPETITIVE SURGE CURRENT


MBR30L300CD

Mos-Controlled Schottky Barrier Rectifiers



OUTLINE DRAWINGS

TO-263




OUTLINE DIMENSIONS

Dim.	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	9.30	-	10.50	0.3661	-	0.4134
B	9.60	-	11.60	0.3780	-	0.4567
C	8.20	-	9.50	0.3228	-	0.3740
D	4.00	-	5.00	0.1575	-	0.1969
E	1.00	-	1.70	0.0394	-	0.0669
F	0.20	-	0.70	0.0079	-	0.0276
G	4.45	-	5.25	0.1752	-	0.2067
H	1.25	-	1.85	0.0492	-	0.0728
J	1.00	-	1.60	0.0394	-	0.0630
K	0.60	-	1.00	0.0236	-	0.0394
L	2.25	-	2.80	0.0886	-	0.1102

RECOMMENDED LAYOUT DRAWINGS

TO-263



OUTLINE DIMENSIONS

Dim.	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	-	10.86	-	-	0.4276	-
B	-	7.86	-	-	0.3094	-
C	-	11.64	-	-	0.4583	-
D	-	5.08	-	-	0.2000	-
E	-	3.62	-	-	0.1090	-
F	-	1.14	-	-	0.0560	-

PACKING INFORMATION

Package Code	Package Method	Min. Pack. Size (mm)	Quantity (Pcs/Min. Pack.)	Inner Box Size L×W×H(mm)	Quantity (Pcs/Inner Box)	Outer Carton Size L×W×H(mm)	Quantity (Pcs/Carton)
TO-263	RL	330	800	340x340x50	800	420x365x360	6400

MBR30L300CD


Mos-Controlled Schottky Barrier Rectifiers



Recommended wave soldering condition

Product	Peak Temperature	Soldering Time
Pb-free devices	260 +0/-5 °C	5 +1/-1 seconds

Recommended temperature profile for IR reflow



Profile feature	Sn-Pb eutectic Assembly	Pb-free Assembly
Average ramp-up rate (T _{smax} to T _p)	3°C/second max.	3°C/second max.
Preheat -Temperature Min(TS min) -Temperature Max(TS max) -Time(ts min to ts max)	100°C 150°C 60-120 seconds	150°C 200°C 60-180 seconds
Time maintained above: -Temperature (TL) - Time (tL)	183°C 60-150 seconds	217°C 60-150 seconds
Peak Temperature(TP)	240 +0/-5 °C	260 +0/-5 °C
Time within 5°C of actual peak temperature(tp)	10-30 seconds	20-40 seconds
Ramp down rate	6°C/second max.	6°C/second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

Note : All temperatures refer to topside of the package, measured on the package body surface.

MBR30L300CD

Mos-Controlled Schottky Barrier Rectifiers



Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from niuhang Electronics Technology co., LTD
- Niuhan Electronics Technology co., LTD. reserves the rights to make changes of the content herein the document anytime without notification.
- Niuhan Electronics Technology co., LTD. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Niuhan Electronics Technology co., LTD. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. niuhang Electronics Technology co., LTD. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify niuhang Electronics Technology co., LTD. for any damages resulting from such improper use or sale.
- When the appearance of the product and chip size does not change, in order to protect the customer's quality, change the internal structure and the production process Niuhan can not notify