



REV.	Q'TY	ECN. NO.	APR.	DATE





Part No	Pin	A	B	C
XY-S2B-PH-SM4-TB	2	2.00	8.00	6.80
XY-S3B-PH-SM4-TB	3	4.00	10.00	8.80
XY-S4B-PH-SM4-TB	4	6.00	12.00	10.80
XY-S5B-PH-SM4-TB	5	8.00	14.00	12.80
XY-S6B-PH-SM4-TB	6	10.00	16.00	14.80
XY-S7B-PH-SM4-TB	7	12.00	18.00	16.80
XY-S8B-PH-SM4-TB	8	14.00	20.00	18.80
XY-S9B-PH-SM4-TB	9	16.00	22.00	20.80
XY-S10B-PH-SM4-TB	10	18.00	24.00	22.80
XY-S11B-PH-SM4-TB	11	20.00	26.00	24.80
XY-S12B-PH-SM4-TB	12	22.00	28.00	26.80
XY-S13B-PH-SM4-TB	13	24.00	30.00	28.80
XY-S14B-PH-SM4-TB	14	26.00	32.00	30.80
XY-S15B-PH-SM4-TB	15	28.00	34.00	32.80
XY-S16B-PH-SM4-TB	16	30.00	36.00	34.80

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatur Range: -25℃ ~+ 85℃



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: WAFER 2.00 间距		
.X±0.2	X.*± 5°	APR. Alex	DWG NO. XY-SMNB-GHS-TB	
.XX±0.1	.X.*± 3°	CHK. Jack	PROJ.  CUSTOMER DRAWING	
.XXX±0.05	.XX.*± 1°	DRA. Can	SIZE A4	SCALE 1:1
		SHEET 1/1		REV. A