

■ **Features**

- Glass passivated chip
- Low reverse leakage current
- High surge current capability
- Fast reverse recovery time

■ **Applications**


- General purpose use in AC/DC bridge full wave rectification

■ **Mechanical Data**

- Case: D3K
- Polarity symbols being marked on body
- Molding compound meets UL 94V-0 flammability rating
- RoHS-compliant, Solder plated, solderable per MIL-STD-750, Method 2026



Reverse Voltage 50-1000 V
Forward Current 8.0 A max



■ **Marking**

- RD3K8(005~10)

■ **Maximum Ratings @ Ta = 25°C unless otherwise noted**

PARAMETER	SYMBOL	UNIT	RD3K8005	RD3K801	RD3K802	RD3K804	RD3K806	RD3K808	RD3K810	
Repetitive peak reverse voltage	V_{RRM}	V	50	100	200	400	600	800	1000	
Maximum RMS voltage	V_{RMS}	V	35	70	140	280	420	560	700	
Maximum DC blocking Voltage	V_{DC}	V	50	100	200	400	600	800	1000	
Maximum average output current@60Hz sine wave, resistance load	$I_{F(AV)}$	A	8.0							
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load	I_{FSM}	A	170							
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load		A	340							
Current squared time @1ms≤t<8.3ms Tj=25°C, Rating of per diode	I^2t	A ² S	119.94							
Maximum reverse recovery time	T_{rr}	ns	150				250		500	
Storage temperature	T_{stg}	°C	-55~+150							
Junction temperature	T_j	°C	-55~+150							

■ **Electrical Characteristics @ Ta = 25°C unless otherwise noted**

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	RD3K8005	RD3K801	RD3K802	RD3K804	RD3K806	RD3K808	RD3K810
Maximum instantaneous forward voltage	$I_F=4.0A$	V_F	V	1.3						
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}, T_j=25°C$	I_R	μA	5						
	$V_R=V_{DC}, T_j=100°C$	I_R		100						

■ **Characteristic Curve (Typical)**




FIG1. Derating Curve For Output Rectified Current




FIG2. Surge Forward Current Capability




FIG3. Typical Forward Characteristics





FIG4. Typical Reverse Characteristics

■ **Marking and packet information**




RD3K*** : Marking Model

TOS : Brand Logo

Packaging information	
每盒	500PCS
每箱	5000PCS
脚长定制	支持

■ **D3K Package outline dimensions**



Dimensions in millimeters

■ **Notice**

XILONG reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product therein. xilong does not assume any liability arising out of the application or use of any product described herein.