




REV.	Q'TY	ECN. NO.	APR.	DATE





Part No	Pin	A	B	C
XY-BM2B-SRSS-TB	2	1.00	4.35	2.60
XY-BM3B-SRSS-TB	3	2.00	5.35	3.60
XY-BM4B-SRSS-TB	4	3.00	6.35	4.60
XY-BM5B-SRSS-TB	5	4.00	7.35	5.60
XY-BM6B-SRSS-TB	6	5.00	8.35	6.60
XY-BM7B-SRSS-TB	7	6.00	9.35	7.60
XY-BM8B-SRSS-TB	8	7.00	10.35	8.60
XY-BM9B-SRSS-TB	9	8.00	11.35	9.60
XY-BM10B-SRSS-TB	10	9.00	12.35	10.60
XY-BM11B-SRSS-TB	11	10.00	13.35	11.60
XY-BM12B-SRSS-TB	12	11.00	14.35	12.60
XY-BM13B-SRSS-TB	13	12.00	15.35	13.60
XY-BM14B-SRSS-TB	14	13.00	16.35	14.60
XY-BM15B-SRSS-TB	15	14.00	17.35	15.60
XY-BM16B-SRSS-TB	16	15.00	18.35	16.60
XY-BM18B-SRSS-TB	18	17.00	20.35	18.60
XY-BM20B-SRSS-TB	20	19.00	22.35	20.60

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.0
- 2.Voltage Rating: 50V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 30mΩ Max
- 6.Withstanding voltage: 250V AC 1/Minute
- 7.Temperatuer Range: -40℃ ~+ 85℃



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.2	X.*± 5'	APR.	Alex	TITLE: WAFER 1.00 封装	
.XX±0.1	.X*± 3'	CHK.	Jack	DWG NO. XY-BMNB-SRSS-TB	
.XXX±0.05	.XX*± 1'	DRA.	Can	PROJ. CUSTOMER DRAWING	
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A