

1


2

3

4

This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	12/7/06	12/7/06



技术特性/Electrical Specifications

特性阻抗/Impedance	50 Ω
频率范围/Frequency Range	DC-18GHz
电压驻波比/VSWR	≤ 1.50
插入损耗/Insert Loss	$\leq 0.06 \times \sqrt{f}$ (f GHz) dB
耐压/Withstanding Voltage	$\geq 750V$
绝缘电阻/Insulation Resistance	$\geq 5000M\Omega$

材料/Material Data

外导体/Outer contact	黄铜/Brass/金 gold Plated
中心导体/Center contact	磷青铜/Phosphor Bronze/金 gold Plated
	聚四氟乙烯/PTFE

绝缘介质/Insulator

连接参数/The connection parameters


耐久性/durability	≥ 500 次 (cycles)
内导体保持力/Center conductor retention	$\geq 0.28N$

环境参数/Environmental Data

温度范围/Temperature Range	-55°C to 155°C
------------------------	----------------

Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 12/07/06	TITLE: RF Coaxial Connector SMA Female Bulkhead Connector For PCB				
ENGINEER: L.yu 12/07/06		 DIMENSION IN MILLIMETERS (mm)			
APPROVED: W.yi 12/07/06		SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A
TOLERANCES UNLESS OTHERWISE SPECIFIED	PART NO: HL3-SMA-KYHD3				
X ± 0.50					
.X ± 0.20					
.XX ± 0.10					
ANGLES $\pm 1^\circ$					