

30-Ampere, 45-200 Voltage Schottky Barrier Metal-Silicon Rectifiers

■ Features


- Metal silicon junction
- Low power loss and high efficiency
- Super fast reverse recovery time
- High surge current capability
- The plastic case material has UL flammability classification rating 94V-0

■ Mechanical Data

- Polarity: As marked
- Lead free complies with the EU ROHS directive
- Terminals: Tin plated leads, solderable per Mil-STD-750 Method 2026

■ Typical applications





- For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, and telecommunication.



■ Maximum Ratings @ Ta = 25°C unless otherwise noted

PARAMETER		SYMBOL	MBR3045***	MBR30100***	MBR30150***	MBR30200***	UNIT
Maximum recurrent peak reverse voltage		V _{RRM}	45	100	150	200	V
Maximum RMS voltage		V _{RSM}	31.5	70	105	140	V
Maximum DC Blocking Voltage		V _{DC}	45	100	150	200	V
Maximum average forward rectified current	Per diode	I _{FM}	15				A
	Per device	I _{FM}	30				
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load		I _{FSM}	200				A
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load			400				A
Current squared time @1ms≤t<8.3ms T _j =25°C, Rating of per diode		I ² t	166.0				A ² S
Maximum instantaneous forward voltage @I _F =I _{FM} (Per diode)		V _F	0.7	0.85	0.90	0.95	V
Maximum DC reverse current at rated DC blocking voltage	T _j =25°C	I _R	0.2				mA
	T _j =100°C	I _R	20				mA
Junction temperature range		T _j	-55~+150				°C
Storage temperature range		T _{STG}	-55~+150				°C

■ Characteristic Curve



■ Package Outline Dimensions (TO-220F)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.5	4.9	0.177	0.193
A1	2.5	2.9	0.098	0.114
b	0.5	0.8	0.020	0.031
b1	1.1	1.4	0.043	0.055
C	0.4	0.6	0.016	0.024
C1	2.4	2.8	0.094	0.110
D	9.5	10.5	0.374	0.413
E	15.5	16.5	0.610	0.650
e	2.45	2.65	0.096	0.104
e1	4.9	5.3	0.193	0.209
F	2.9	3.5	0.114	0.138
L	12.5	13.5	0.492	0.531
L1	2.8	3.2	0.110	0.126
d	3.4	3.6	0.134	0.142

■ Package Outline Dimensions (TO-220AB)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.3	4.7	0.169	0.185
A1	2.4	2.9	0.094	0.114
b	0.7	0.9	0.028	0.035
b1	1.2	1.4	0.047	0.055
C	0.3	0.5	0.012	0.020
C1	1.1	1.3	0.043	0.051
D	9.5	10.5	0.374	0.413
E	8.50	8.90	0.335	0.350
E1	12.00	12.50	0.472	0.492
e	2.44	2.64	0.096	0.104
e1	4.88	5.26	0.192	0.207
F	2.60	2.80	0.102	0.110
L	13.00	14.00	0.512	0.551
L1	3.80	4.20	0.150	0.165

■ Package Outline Dimensions (TO-252)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	2.1	2.6	0.083	0.102
A1	-	0.15	-	0.006
A2	2.0	2.5	0.079	0.098
B	1.1	1.6	0.043	0.063
b	0.5	0.8	0.020	0.031
b1	0.6	0.9	0.024	0.035
C	0.3	0.6	0.012	0.024
C1	0.3	0.6	0.012	0.024
D	6.1	6.7	0.240	0.264
D1	5.0	5.6	0.197	0.220
E	5.2	5.8	0.205	0.228
e	2.1	2.5	0.083	0.098
e1	4.2	4.9	0.165	0.193
L	9.5	10.5	0.374	0.413
L1	2.5	3.5	0.098	0.138
L2	1.2	1.8	0.047	0.071
L3	0.8	1.5	0.031	0.059
θ	0°	10°	0°	10°


■ Package Outline Dimensions (TO-263)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A1	0	0.3	0.000	0.012
B	1.3	1.4	0.051	0.055
b	0.7	0.8	0.028	0.031
b1	1.3	1.5	0.051	0.059
b2	0.7	0.8	0.028	0.031
C	4.4	4.7	0.173	0.185
C1	1.1	1.3	0.043	0.051
C2	2.5	2.8	0.098	0.110
C3	0.3	0.4	0.012	0.016
D	9.5	10.5	0.374	0.413
E	9.5	10.5	0.374	0.413
e	2.4	2.6	0.094	0.102
L	13.5	16.0	0.531	0.630
L1	4.5	5.5	0.177	0.217
L2	2.0	3.0	0.079	0.118
L3	1.0	1.6	0.039	0.063
θ	5°	10°	5°	10°

■ Ordering information

Package	Order code	Base quantity	Box quantity	Carton quantity
TO-220F/ITO-220AB	MBR20***FCT	50pcs/tube	1000pcs/box	5000pcs/cartoon
TO-220/TO-220AB	MBR20***CT	50pcs/tube	1000pcs/box	5000pcs/cartoon
TO-263	MBR20***DC	800pcs/reel	1600pcs/box	8000pcs/cartoon
TO-252	MBR20***CS	2500pcs/reel	5000pcs/box	25000pcs/cartoon

■ Suggested thermal profiles for soldering processes



Notice

XILONG reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. xilong does not assume any liability arising out of the application or use of any product described herein.